

1.81	0.32
\$1.02	0.72
\$2.28	0.90
\$4.31	1.70
\$1.57	1.80
\$4.82	1.90
\$6.09	2.40
7.36	2.90
13.20	5.20
17.01	6.70
20.82	8.20
23.36	9.20
26.92	1.060
35.05	1.380
43.68	1.720
6.35	2.20
33.02	1.300

TOGGLE LEVER, BRASS, CHR. PLT.

- HEX NUT, STEEL

-BUSHING, 15/32-32UNS-2ATHD.
HOUSING, ZINC DIE CAST

TERMINAL, STEEL

-SCREW-SEMS
8-32 X 6.35 LG., STEEL
-BAT #1 (6 REQ'D)

-BAT. #1

CIRCUIT #1
CIRCUIT #2

BAT#2

CIRCUIT #

-CIRCUIT #2

NOTE:

Ⓜ ALL STEEL PARTS PLATED

2. HEX NUT & SCREWS TO BE

⑦ BAGGED

DO NOT SCALE

DATE DRAWN
2-25-64

DATE BLUEPRINT

COLE-HERSEE COMPANY
BOSTON, MASS. 02127, U.S.A.

BOSTON, MASS. 02127, U.S.A.

D.P.D.T. TOGGLE SW.

551806

METRIC

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRVD.	SCALE	DATE DRAWN
								—	MF	LB		1:1	2-25-64
								FINISH —	COLE-HERSEE COMPANY BOSTON, MASS. 02127, U.S.A.				DATE BLUEPRINT
				N	EC401005	1/4/01	PS						
				M	2852534	11/19/25	JK	TOLERANCES FRACTIONAL ± DECIMAL ±.25					
				L	REDRAWN	10.1.76	KG		D.P.D.T. TOGGLE SW.				551806