



CURREN RATE [A]	VERSIONS AND PART NUMBERS
40	3298040.Z
60	3298060.Z
80	3298080.Z
100	3298100.Z
125	3298125.Z
150	3298150.Z
175	3298175.Z
200	3298200.Z
225	3298225.Z
250	3298250.Z
300	3298300.ZXSTA
350	3298350.ZXSTA
400	3298400.ZXSTA
500	3298500.ZXSTA
600	3298600.ZXSTA
SHUNT	3298900.Z



LTR	DATE	REVISION	DRW
A	01/FEB/23	526138GCA - INITIAL RELEASE	OPL



ISOMETRIC VIEW



Ø M8: Ø 8.5 (40A-250A-SHUNT)
M6: Ø 6.5 (300A-600A)



SINGLE ZCASE 32V						
TERMINAL MATERIAL :			COPPER			
TERMINAL PLATING :			TIN			
HOUSING MATERIAL :			PPA-GF33HS (U.L. 94 FLAMMABILITY RATING - HB)			
INSULATING TUBE :			CERAMIC			
LINEAR DIMENSIONS					ANGLES	RADII
DIM	.5 - 6	6 - 30	30 - 120	120 - 400	±0.5°	±0.2
TOL	±0.1	±0.2	±0.3	±0.5		
 Littelfuse® CHICAGO, USA 773-628-1000			REVISION		DRWG. NO.	
			A		WEB-3298000.Z	