

注释：我们正在更新系统，您可能会注意到遗失/过时的数据。在此过渡时期，请参考您的合规证书或在 <https://www.ul.com/about/locations> 上联系客服中心。

Auxiliary Devices - Component

COMPANY

LITTELFUSE INC

8755 W Higgins Rd, Suite 500
Chicago, IL 60631 United States

E61760

Marking: Company name or trademark  , and model designation.

Note: For additional marking information, refer to the [Guide Information Page](#).

View model for additional information

Auxiliary Devices, Model(s): [57155-000](#)

Auxiliary Devices, Model(s): [59001\(b\)](#), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Auxiliary Devices, Model(s): [59001x](#) where x can be a string of up to 5 alphanumeric characters.

Auxiliary Devices, Model(s): [59020x](#) where x can be a string of up to 5 alphanumeric characters.

Auxiliary Devices, Model(s): [59021x](#) where x can be a string of up to 5 alphanumeric characters.

Auxiliary Devices, Model(s): [59143](#) followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Auxiliary Devices, Model(s): [59155x](#) where x can be a string of up to 5 alphanumeric characters

Auxiliary Devices, Model(s): [59156x](#) where x can be a string of up to 5 alphanumeric characters

Auxiliary Devices, Model(s): [59177x](#) where x can be a string of up to 5 alphanumeric characters.

Magnet actuators, Model(s): [5701](#), [57022-000-1](#), [57025-000-1](#), [57030-000-1](#), [57040-000-1](#), [57045-000-1](#), [57050-000-1](#), [57065-000-1](#), [57066-000](#), [57070-000-1](#), [57071-000-1](#), [57105-000](#), [57125-000](#), [57135-000](#), [57145-000-1](#), [57150-000-1](#), [5805](#), [5858](#)

Proximity switches for use in industrial applications, Model(s): [5800\(a\)](#), [5801\(a\)](#), [5802\(a\)](#), [5804\(a\)](#), [59015-010](#), [59015-1](#), [59025-541](#) followed by X, [59070-514](#) followed by X, [59070-515](#) followed by X, [59135\(a\)](#), [59166](#) and [59170](#) followed by X, [59600-413](#) followed by X

Proximity switches for use in industrial applications, Model(s): [59022\(b\)](#), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): [59025\(b\)](#), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): [59030\(b\)](#), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59040(b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59045 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59050 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59065 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59066 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59070 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59071 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59085 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59086 followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59105 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59110 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59125 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59140 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59141 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59145 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59150 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59160 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59165 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59200 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59210 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Proximity switches for use in industrial applications, Model(s): 59220 (b), followed by X, followed by -1 to -9, -010, -020, -030, -040, -050, -700 to 725, -800 to -999.

Solid state reed switches, Model(s): 59600-164, 59600-165

Last Updated on 2023-10-13

并不是所有出现在本数据库中的公司名称和产品都满足了UL跟踪检验服务的要求。只有带有UL标志的产品，才应该被视为经过UL认证，并满足UL跟踪检验服务的要求。注意查看产品上的标志。

UL允许在线认证目录中所含材料的复制遵循以下条件：1.指南信息、装配、构造、设计、系统和/或认证（文件）必须在不篡改任何数据（或图纸）的情况下完整且无误导性地呈现。2.“经UL允许从在线认证目录转载”声明必须出现在所摘取材料的邻近位置。此外，转载材料必须包含以下格式的版权声明：“©2023 UL LLC.”