

# ATO® 155 SERIES

## 32V STACKABLE IN-LINE PANEL-MOUNT FUSE HOLDER WITH LOOPED WIRE LEADS



08680062H

### Description

The ATO® 155 Series 32V Stackable In-Line Panel-Mount Fuse Holder with Looped Wire Leads makes it simple to install an ATO® or FKS blade-style automotive fuse (sold separately unless indicated).

Configurations with black 14 AWG leads are compatible with fuses up to 20 amps, while models of the panel-mount fuse holder with orange 10 AWG leads accept fuses up to 30 amps.

The stackable fuse holder can also be used with additional ATO® 155 Series fuse holders to create a fuse block for multiple fuses.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/ATO155](http://littelfuse.com/ATO155)

### Ordering Information

| PART NUMBER             | DESCRIPTION   | FUSE TYPE | MOUNTING METHOD     | MAX CURRENT RATING | MAX VOLTAGE RATING |
|-------------------------|---|-----------|---------------------|--------------------|--------------------|
| 01550300LXN, W/O Fuse   | 32V Stackable In-Line Panel-Mount Fuse Holder with Black 14 AWG Looped Wire Leads               | ATO       | IN LINE FUSE HOLDER | 20 Amps            | 32V                |
| 01550310ZXA, W/FUSE 10A | 32V Stackable In-Line Panel-Mount Fuse Holder with Black 14 AWG Looped Wire Leads and 10A Fuse  | ATO       | IN LINE FUSE HOLDER | 10Amps             | 32V                |
| 01550320ZXA, W/FUSE 20A | 32V Stackable In-Line Panel-Mount Fuse Holder with Black 14 AWG Looped Wire Leads and 20A Fuse  | ATO       | IN LINE FUSE HOLDER | 20Amps             | 32V                |
| 01550320ZXU, W/O Fuse   | 32V Stackable In-Line Panel-Mount Fuse Holder with Terminals for 14 AWG Wire                    | ATO       | IN LINE FUSE HOLDER | 20 Amps            | 32V                |
| 01550400Z, W/O Fuse     | 32V Stackable In-Line Panel-Mount Fuse Holder with Orange 10 AWG Looped Wire Leads              | ATO       | IN LINE FUSE HOLDER | 30 Amps            | 32V                |
| 01550430ZXA, W/FUSE 30A | 32V Stackable In-Line Panel-Mount Fuse Holder with Orange 10 AWG Looped Wire Leads and 30A Fuse | ATO       | IN LINE FUSE HOLDER | 30Amps             | 32V                |
| 01550430ZXU, W/O Fuse   | 32V Stackable In-Line Panel-Mount Fuse Holder with Terminals for 10 AWG Wire                    | ATO       | IN LINE FUSE HOLDER | 30 Amps            | 32V                |
| 08680062H, W/O Fuse     | 32V Stackable In-Line Panel-Mount Fuse Holder Body  | ATO       | IN LINE FUSE HOLDER | N/A                | N/A                |
| 01550300Z, W/O Fuse     | 32V Stackable In-Line Panel-Mount Fuse Holder with Black 14 AWG Looped Wire Leads               | ATO       | IN LINE FUSE HOLDER | 20 Amps            | 32V                |
| 868-062-000UL, W/O Fuse | 32V Stackable In-Line Panel-Mount Fuse Holder UL Body   | ATO       | IN LINE FUSE HOLDER | N/A                | N/A                |
| 913-008                 | Crimp Terminal with Insulation Grip - 14 Gauge, Reel  | N/A       | CRIMPED             | N/A                | N/A                |
| 913-008-001             | Crimp Terminal with Insulation Grip - 14 Gauge  | N/A       | CRIMPED             | N/A                | N/A                |
| 913-008-R               | Crimp Terminal with Insulation Grip - 14 Gauge, Reverse Reel                                    | N/A       | CRIMPED             | N/A                | N/A                |
| 868-062-000, W/O Fuse   | 32V Stackable In-Line Panel-Mount Fuse Holder Body  | ATO       | IN LINE FUSE HOLDER | N/A                | N/A                |
| 913-007                 | Crimp Terminal with Insulation Grip - 10 Gauge, Reel  | N/A       | CRIMPED             | N/A                | N/A                |
| 913-007-001             | Crimp Terminal with Insulation Grip - 10 Gauge  | N/A       | CRIMPED             | N/A                | N/A                |
| 01550400LXN W/O Fuse    | 32V Stackable In-Line Panel-Mount Fuse Holder with Orange 10 AWG Looped Wire Leads              | ATO       | IN LINE FUSE HOLDER | 30 Amps            | 32V                |

### Specifications

|                            |                           |
|----------------------------|---------------------------|
| <b>Max Current Rating:</b> | 30 Amps, 20 Amps, 10 Amps |
| <b>Fuse Type:</b>          | ATO®                      |
| <b>Mounting Method:</b>    | IN LINE FUSE HOLDER       |
| <b>Max Voltage Rating:</b> | 32 V                      |

### Applications

- Automotive
- Electronics
- Small Auxiliary Circuit Protection

### Features and Benefits

- Accepts ATO® or FKS blade fuses (sold separately unless indicated) up to 20 amps or 30 amps
- Configurations available with either black 14 AWG leads or orange 10 AWG leads to suit different applications
- Stackable fuse holder body can be paired with additional ATO® 155 Series fuse holders to create a multi-fuse block
- Various fuse holder component parts are also available separately, including the body, UL body, and crimp terminals for the different wire gauges