



ATO<sup>®</sup> Shunt

## ATO<sup>®</sup> Shunt

### Specifications

*Recommended Environmental Temp.:	-40°C to +125°C
Max. Continuous Load Rating:	35A **
Housing Material:	Thermoplastic (UL 94 Flammability Rating V0)
Terminal Material:	Tin Plated Brass



\*Tin plating's temperature limit is ≈130°C

\*\*Rating varies based on mating terminal performance

### Ratings

Part Number	Max Continuous Load Rating** (A)	Housing Material	Terminal Material	Part Quantity
02400094P	35	Thermoplastic (UL 94V0)	Tin Plated Brass	2000