


HiPerFRED²

V_{RRM}	=	200 V
I_{FAV}	=	10 A
t_{rr}	=	35 ns

High Performance Fast Recovery Diode
 Low Loss and Soft Recovery
 Single Diode


Part number

DPG10I200PM



Backside: isolated

 E72873



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: TO-220FP

- Isolation Voltage: 2500 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Soldering pins for PCB mounting
- Base plate: Plastic overmolded tab
- Reduced weight


Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Fast Diode				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				200	V
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				200	V
I _R	reverse current, drain current	V _R = 200 V	T _{VJ} = 25°C			1	μA
		V _R = 200 V	T _{VJ} = 150°C			0.06	mA
V _F	forward voltage drop	I _F = 10 A	T _{VJ} = 25°C			1.27	V
		I _F = 20 A				1.45	V
		I _F = 10 A	T _{VJ} = 150°C			0.98	V
		I _F = 20 A				1.17	V
I _{FAV}	average forward current	T _C = 125°C rectangular d = 0.5	T _{VJ} = 175°C			10	A
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 175°C		0.74	V
r _F	slope resistance					17.7	mΩ
R _{thJC}	thermal resistance junction to case					4.4	K/W
R _{thCH}	thermal resistance case to heatsink				0.5		K/W
P _{tot}	total power dissipation	T _C = 25°C				35	W
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		140	A
C _J	junction capacitance	V _R = 150 V f = 1 MHz		T _{VJ} = 25°C	15		pF
I _{RM}	max. reverse recovery current	} I _F = 10 A; V _R = 130 V -di _F /dt = 200 A/μs		T _{VJ} = 25 °C	3		A
t _{rr}	reverse recovery time			T _{VJ} = 125 °C	5.5		A
				T _{VJ} = 25 °C	35		ns
				T _{VJ} = 125 °C	45		ns

Package TO-220FP				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
I_{RMS}	RMS current	per terminal				35	A
T_{VJ}	virtual junction temperature			-55		175	°C
T_{op}	operation temperature			-55		150	°C
T_{stg}	storage temperature			-55		150	°C
Weight					2		g
M_D	mounting torque			0.4		0.6	Nm
F_C	mounting force with clip			20		60	N
$d_{Spp/App}$	creepage distance on surface striking distance through air	terminal to terminal	3.2	2.7			mm
$d_{Spb/Apb}$		terminal to backside	2.5	2.5			mm
V_{ISOL}	isolation voltage	t = 1 second	50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA	2500			V
		t = 1 minute		2100			V

Product Marking



Part description

D = Diode
 P = HiPerFRED
 G = extreme fast
 10 = Current Rating [A]
 I = Single Diode
 200 = Reverse Voltage [V]
 PM = TO-220ACFP (2)

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DPG10I200PM	DPG10I200PM	Tube	50	503771


Similar Part	Package	Voltage class
DPG10I200PA	TO-220AC (2)	200

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 175^\circ\text{C}$

		Fast Diode	
$V_{0\max}$	threshold voltage	0.74	V
$R_{0\max}$	slope resistance *	14.5	mΩ

Outlines TO-220FP


Note:
 All metal surface are
 matte pure tin plated
 except trimmed area.

Dim.	Millimeters		Inches	
	min	max	min	max
A	4.50	4.90	0.177	0.193
A1	2.34	2.74	0.092	0.108
A2	2.56	2.96	0.101	0.117
b	0.70	0.90	0.028	0.035
b1	1.27	1.47	0.050	0.058
c	0.45	0.60	0.018	0.024
D	15.67	16.07	0.617	0.633
d1	0	1.10	0	0.043
E	9.96	10.36	0.392	0.408
e	2.54 BSC		0.100 BSC	
H	6.48	6.88	0.255	0.271
L	12.68	13.28	0.499	0.523
L1	3.03	3.43	0.119	0.135
$\varnothing P$	3.08	3.28	0.121	0.129
Q	3.20	3.40	0.126	0.134




Fast Diode


Fig. 1 Forward current
 I_F versus V_F




Fig. 2 Typ. reverse recov. charge
 Q_{rr} versus $-di_F/dt$




Fig. 3 Typ. reverse recov. current
 I_{RR} versus $-di_F/dt$




Fig. 4 Typ. dynamic parameters
 Q_{rr} , I_{RR} versus T_{VJ}




Fig. 5 Typ. reverse recov. time
 t_{rr} versus $-di_F/dt$




Fig. 6 Typ. forward recov. voltage
 V_{FR} and t_{fr} versus di_F/dt




Fig. 7 Typ. recovery energy
 E_{rec} versus $-di_F/dt$




Fig. 8 Transient thermal resistance junction to case