

Military Midget 10x38 mm Fuses

592S Series

Commercial Equivalent = [KLK Series](#)



Description

With a vast network of manufacturing and engineering facilities and a global system of distribution channels, Littelfuse offers a variety of switchgear fuses to meet your specific needs, including military high-reliability fuses.

Features & Benefits

FEATURES	BENEFITS
10x38 mm size	Common dimensions used in a variety of applications
Fast-acting	Provides fast, reliable short-circuit response within the interrupting rating
POWR-GARD® technology	Ensures quality overcurrent protection

Applications

- Control circuits
- Street and HID lighting
- Computers

Approved to MIL-PRF-15160/60

MIL TYPE DESIGNATION	SILVER-PLATED CAPS	MIL TYPE DESIGNATION	SILVER-PLATED CAPS
60C 500V ¼AS	592.125S	F60C 500V 3AS	592.003S
F60C 500V ⅜AS	592.200S	F60C 500V 4AS	592.004S
F60C 500V ½AS	592.250S	F60C 500V 5AS	592.005S
F60C 500V ¾AS	592.300S	F60C 500V 6AS	592.006S
F60C 500V 1AS	592.375S	F60C 500V 8AS	592.008S
F60C 500V 1½AS	592.500S	F60C 500V 10AS	592.010S
F60C 500V 2AS	592.750S	F60C 500V 15AS	592.015S
	592.001S	F60C 500V 20AS	592.020S
	592.01.5S	F60C 500V 25AS	592.025S
	592.002S	F60C 500V 30AS	592.030S

Note: Boldface numbers indicate series; light type numbers indicate amperage value.

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.