


# POWR-GARD® Fuses

## CNN\_E Series Lift Truck

80 V dc • Very Fast-Acting • 35 - 800 A



### Description

CNN\_E fuses are rated for applications up to 80 V dc. As fork lift trucks and electrical vehicle system voltages increase, circuit protection needs to be rated higher than the standard CNN products to handle the increased voltage. The CNN\_E is considered very fast-acting for quicker reaction time.

### Features & Benefits

- Up to 80 V dc protection
- Up to 2,700 A interrupting rating
- Compact size saves space
- RoHS compliant and lead (Pb) free

### Applications

- Lift trucks
- Scissor lifts
- Pallet movers
- Low voltage battery powered equipment
- Data center

### Specifications

<b>Voltage Rating</b>	80 V dc
<b>Ampere Ratings</b>	35 - 800 A
<b>Max. Interrupting</b>	2,700 A
<b>Environmental</b>	RoHS Compliant, Lead (Pb) Free
<b>Country of Origin</b>	Mexico

### Certification & Compliance

cURus

cURus (File E71611)

# POWR-GARD® Fuses

## CNN\_E Series Lift Truck

### Ordering Information

AMPERE RATING (A)	CATALOG NUMBER	PRODUCT MARKING	PACKING QUANTITY	ORDERING NUMBER	UPC CODE
35	CNN035E	CNN035E	5	0CNN035E.V	07945818319
40	CNN040E	CNN040E	5	0CNN040E.V	07945818320
50	CNN050E	CNN050E	5	0CNN050E.V	07945818321
60	CNN060E	CNN060E	5	0CNN060E.V	07945818322
			100	0CNN060E.H	07945824328
80	CNN080E	CNN080E	5	0CNN080E.V	07945818323
			100	0CNN080E.H	07945824329
90	CNN090E	CNN090E	5	0CNN090E.V	07945818324
			100	0CNN090.H	07945824330
100	CNN100E	CNN100E	5	0CNN100E.V	07945818325
			100	0CNN100E.H	07945824331
125	CNN125E	CNN125E	5	0CNN125E.V	07945818326
			100	0CNN125E.H	07945824332
150	CNN150E	CNN150E	5	0CNN150E.V	07945818327
			100	0CNN150E.H	07945824333
175	CNN175E	CNN175E	5	0CNN175E.V	07945818328
			100	0CNN175E.H	07945824334
200	CNN200E	CNN200E	5	0CNN200E.V	07945818329
			100	0CNN200E.H	07945824335
225	CNN225E	CNN225E	5	0CNN225E.V	07945818330
			100	0CNN225E.H	07945824336
250	CNN250E	CNN250E	5	0CNN250E.V	07945818331
			100	0CNN250E.H	07945824337
275	CNN275E	CNN275E	5	0CNN275E.V	07945818332
			100	0CNN275E.H	07945824338
300	CNN300E	CNN300E	5	0CNN300E.V	07945818333
			100	0CNN300E.H	07945824339
325	CNN325E	CNN325E	5	0CNN325E.V	07945818334
350	CNN350E	CNN350E	5	0CNN350E.V	07945818335
400	CNN400E	CNN400E	5	0CNN400E.V	07945818336
			100	0CNN400E.H	07945829772
500	CNN500E	CNN500E	5	0CNN500E.V	07945818337
600	CNN600E	CNN600E	5	0CNN600E.V	07945818338
700	CNN700E	CNN700E	5	0CNN700E.V	07945818339
800	CNN800E	CNN800E	5	0CNN800E.V	07945818340

# POWR-GARD® Fuses

## CNN\_E Series Lift Truck

### Dimensions Inches (mm)




FIGURE 1




FIGURE 2

AMPERE RATING (A)	FIGURE
35	1
40	1
50	1
60	1
80	1
90	1
100	2
125	1
150	2
175	1
200	1
225	1
250	1
275	1
300	1
325	2
350	2
400	2
500	2
600	2
700	1
800	1

**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/product-disclaimer](http://www.littelfuse.com/product-disclaimer).