

# 00560900 & 00561100 CONNECTORS

Converter 12V trailer from a 24V vehicle • ISO 1185 • ISO 3731 • ISO 11446 • ISO 1724



## Description

Converter to supply a 12V trailer from a 24V vehicle system as short adapter with a 7 contact connector and a 13 contact socket.

ATTENTION: for bulbs and LEDs only!

## Features and Benefits

- simply plug in between.
- fulfills the law requirement for fail-safe by 100% separated lines.
- compatible with lamp control circuits.
- correct function of ABS-info-module is guaranteed.
- internal short circuit and overload protection, one each line.
- power reserves in case of additional lamps at the trailer.
- European approval e1 023023.

## Specifications Overview

<b>Voltage:</b>	12V/24V
<b>Standards:</b>	ISO 11446
	ISO 1724
	ISO 1185
	ISO 3731
	ISO 3732

## Web Resources

Download technical resources at:

**[littelfuse.com/connectors](http://littelfuse.com/connectors)**

## Ordering Information

PART NUMBER	ISO	CONVERTER DESCRIPTION	TYPE*	PIN MATERIAL	TEMPERATURE RANGE
00560900	11446 1185	13 pole socket 12V to 7 pole plug 24V	N	Nickel-plated brass	-40° to +75°
00561000	1724 1185	7 pole socket 12V to 7 pole plug 24V	N	Nickel-plated brass	-40° to + 75°
00561100	3732 3731	7 pole socket 12V to 7 pole plug 24V	S	Nickel-plated brass	-40° to + 75°

\* N = normal

S = supplementary