

## MPU-32 SUPPLEMENTAL SUPPLY VOLTAGE RATING

The stated MPU-32-0X-XX CSA/UL supply rating is 120-240 Vac (+10%, -45%) and 110-250 Vdc (+10%, -25%). This is equivalent to 65 to 265 Vac and 80 to 275 Vdc. The specifications were written with the +10%, -45% and -25% ratings to meet the requirements of CSA standard C22.2 No. 14, and the UL standards 508 and 1053.

The MPU-32 terminal blocks have a manufacturer specified voltage rating of 300 Vac/dc, however the MPU-32 has been tested and will operate safely at voltages up to 300 Vac and 370 Vdc.