

00504800 & 00599100 CONNECTORS

7/13-Pole Plastic Body Special Sockets • 12V • ISO 1724 • ISO 11446



Specifications Overview

Voltage:	12V
Standards:	ISO 1724 ISO 3732 ISO 11446

Web Resources

Download technical resources at:
littelfuse.com/connectors

Description

Included in the range of sockets are also the following special versions:

- connector 7 pole 12V with 2 pole socket
- 13 pole 12V parking socket
- 13 pole 12V coupling socket
- 7 pole 12V coupling socket ISO 1724
- 7 pole 12V coupling socket ISO 3732
- waterproof socket 220V 16A for camper or caravan

Features and Benefits

- Standards: Conforms to ISO 1724, ISO 3732 & 11446 recommendations and standards.
- Accepts all 7-pole plugs that conform to ISO 1724, ISO 3732 & ISO 11446.

Accessories

PART NUMBER	BULK	IMG.	SOCKET	DESCRIPTION OF ACCESSORIES
00603300 (10 pcs)	00603360 (100 pcs)	1	00421000	Rear rubber gasket for 13 pole 12V coupling socket
00605800 (20 pcs)	00605890 (200 pcs)	2	00421600	Rear rubber gasket for parking socket
00607100 (24 pcs)	00607160 (200 pcs)	3	00504800	Rear rubber gasket for 7 pole+2pole 12V

Ordering Information

PART NUMBER			ISO	PIN MATERIAL	DESCRIPTION
BULK 20 pcs.	BULK 100 pcs.	BULK 100 pcs. <input checked="" type="checkbox"/>			
00504800	00504890	00504899	1724	Brass	connector 7 pole 12V + 2 pole socket
00524800			1724	Brass	connector 7 pole 12V + 2 pole socket
00549700		00549799	1724	Brass	7 pole 12V coupling socket
00549800			3732	Brass	7 pole 12V coupling socket
00421000			11446	Nickel-plated brass	13 pole 12V coupling socket flat
00421600				Brass	13 pole 12V parking socket
00599100				Brass	waterproof socket 220V 16A

