



产品认证证书

证书编号: CQC16001159722

申请人名称及地址

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 美国

制造商名称及地址

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 美国

生产企业名称及地址

昆山利韬电子有限公司 (V015036)
江苏省昆山综合保税区B区中央大道389号

产品名称和系列、规格、型号

热敏电阻 (限流型)

见附件

产品标准和技术要求

GB14536.1-2008; GB/T7153-2002; GB8898-2011

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471553-2015认证规则的要求, 特发此证。

发证日期: 2016年11月30日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

经中国合格评定国家认可委员会认可 CNAS C001-P

主任: _____



中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0090410



PRODUCT CERTIFICATE

No.: CQC16001159722

NAME AND ADDRESS OF THE APPLICANT

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 USA

NAME AND ADDRESS OF THE MANUFACTURER

Littelfuse Inc.
8755 West Higgins Road Chicago, IL 60631 USA

NAME AND ADDRESS OF THE FACTORY

Littelfuse Electronics (Kunshan) Co.,Ltd (V015036)
No.389 Central Avenue, B Zone EPZ, Kunshan City, Jiangsu 215301 PRC

NAME, MODEL AND SPECIFICATION

Polyswitch PPTC

See Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB14536.1-2008;GB/T7153-2002;GB8898-2011

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471553-2015.

Date of issue: Nov.30,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Accredited by China National Accreditation Service for Conformity Assessment CNAS C001-P

President:


Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0090410



产品认证证书

附录:

第 1 页 共 1 页

证书编号: CQC16001159722

纸号: 90410

RXEF005 (7.30-11.10 Ω)、RXEF010 (2.50-4.50 Ω)、RXEF017 (3.30-5.21 Ω)、RXEF020 (1.83-2.75 Ω)、RXEF025 (1.25-1.95 Ω)、RXEF030 (0.88-1.33 Ω)、RXEF040 (0.55-0.86 Ω)、RXEF050 (0.50-0.77 Ω)、RXEF065 (0.31-0.48 Ω)、RXEF075 (0.25-0.40 Ω)、RXEF090 (0.20-0.31 Ω)、RXEF110 (0.15-0.25 Ω)、RXEF135 (0.12-0.19 Ω)、RXEF160 (0.09-0.14 Ω)、RXEF185 (0.08-0.12 Ω)、RXEF250 (0.05-0.08 Ω)、RXEF300 (0.04-0.06 Ω)、RXEF375 (0.03-0.05 Ω)

非绝缘型, 气候类别40/85/21。动作温度: 85 $^{\circ}\text{C}$, 额定电压: RXEF005、RXEF010、RXEF017: 60VDC, 其余型号: 72VDC

注: 此附录与证书同时使用时有效。

主任: _____



中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>