



## JGFI.E184655 Universal Modular Fuses

Page Bottom

### Universal Modular Fuses

[See General Information for Universal Modular Fuses](#)

**LITTELFUSE INC**  
800 E NORTHWEST HWY  
DES PLAINES, IL 60016 USA

E184655

Fuse	Mounting	A Range	Type	V	Interrupting Rating (Breaking Capacity)
Series 455	Surface	0.4, 0.5, 1, 1.6	F	125 ac/dc	50A
Series 464	Surface	250mA, 350mA, 400mA, 500mA, 630mA, 800mA,	F	250 ac	100A
		1, 1.25, 1.6, 2, 2.5, 3.15, 4, 5, 6.3			
Series 465	Surface	250mA, 350mA, 400mA, 500mA, 630mA, 800mA,	T	250 ac	100A
		1, 1.25, 1.6, 2, 2.5, 3.15, 4, 5, 6.3			

Last Updated on 2003-01-30

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2008 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2008 Underwriters Laboratories Inc.®"

An independent organization working for a safer world with integrity, precision and knowledge.

