




TOP VIEW



FRONT VIEW



SIDE VIEW



MOUNTING DETAIL

RATINGS

MAXIMUM VOLTAGE	14,400 Vac
MAXIMUM CURRENT	144 mA
RESISTANCE	100 kΩ
THERMAL	
14,400 Vac	1 MINUTE ON, 120 MINUTES OFF
2,500 Vac	CONTINUOUS
TORQUE	
TERMINAL N	9.0 N–m (80 in–lb)

NOTES

1. DIMENSIONS IN MILLIMETERS [INCHES]
2. TERMINAL–BLOCK SCREWS: 6–32 x 0.25.
3. MOUNTING SCREWS: M6 OR 0.25–20.
4. USE LIQUID–TIGHT FITTING FOR TERMINAL–BLOCK–ENCLOSURE CABLE ENTRY.
5. CERTIFICATIONS NOT SHOWN.

DESCRIPTION	REV.	DATE
RELEASE TO WEB	A	15NOV13

Littelfuse

DWG. NO. ER–25KV	REV. A