# CURRENT TRANSFORMERS

## Instrumentation and metering transformers




**Donut Style** **Foot Mounted**

## Description

Littelfuse offers a wide array of instrument rated current transformers in 1-3 inch diameter opening.


Voltage class: 600V

BIL rating: 10kV


Certification: cURus (WICC File E100575)

## Dimensional Drawing

DONUT STYLE




FOOT MOUNTED WITH BRASS TERMINALS




## Ordering Information

| DONUT MODEL | WINDOW | CURRENT RATIO |
|---|---|---|
| CT-0050-D10 | 1.0" | 50:5 |
| CT-0075-D10 | 1.0" | 75:5 |
| CT-0100-D10 | 1.0" | 100:5 |
| CT-0150-D10 | 1.0" | 150:5 |
| CT-0200-D10 | 1.0" | 200:5 |
| CT-0300-D10 | 1.0" | 300:5 |
| CT-0200-D20 | 2.0" | 200:5 |
| CT-0300-D20 | 2.0" | 300:5 |
| CT-0400-D20 | 2.0" | 400:5 |
| CT-0500-D20 | 2.0" | 500:5 |

| FOOTED MODEL | WINDOW | CURRENT RATIO |
|---|---|---|
| CT-0050-F10 | 1.0" | 50:5 |
| CT-0100-F10 | 1.0" | 100:5 |
| CT-0150-F10 | 1.0" | 150:5 |
| CT-0200-F10 | 1.0" | 200:5 |
| CT-0300-F10 | 1.0" | 300:5 |
| CT-1200-F15 | 1.5" | 1200:5 |
| CT-0150-F20 | 2.0" | 150:5 |
| CT-0200-F20 | 2.0" | 200:5 |
| CT-0300-F20 | 2.0" | 300:5 |
| CT-0400-F20 | 2.0" | 400:5 |
| CT-0600-F20 | 2.0" | 600:5 |
| CT-0400-F30 | 3.0" | 400:5 |
| CT-0800-F30 | 3.0" | 800:5 |

## Part Numbering System

**CT - xxx - D10**

**Series**

**Current Ratio**
xxx:5 current ratio

**Window Size**
10 = 1.0 inch
15 = 1.5 inches
20 = 2.0 inches
30 = 3.0 inches

**Style**
D = Donut Style
F = Footed Style

**Disclaimer Notice** – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at **www.littelfuse.com/product-disclaimer.**