


# BATTERY STUDS

## POWER DISTRIBUTION ACCESSORIES



46210-10



46210-05

### Description

Use to make easily-accessible battery connections, inside or outside the vehicle. They can be used individually or in pairs and are easy to install. Jumper terminals have contact post 13/16" (20.6mm) diameter, 1 1/8" (28.8mm) long, which is grooved to accept standard jumper cables 6 -48V DC.

### Features and Benefits

- Color-coordinated to serve as easy-to-identify power points
- Easy to install for quick distribution of power
- Brass core ensures high conductivity
- Impact-resistant plastic bodies

### Ordering Information

Ordering Information can be found on Page 2.

### Specifications

<b>Insulator Material:</b>	Plastic PBT
<b>Operating Temp Range:</b>	-40°C TO 105°C
<b>Max Continuous Current:</b>	285
<b>Max Continuous Voltage:</b>	36V
<b>Mounting Torque:</b>	10.8-13.5 Nm
<b>Stud Material:</b>	Brass
<b>Washer Material:</b>	Brass

### Applications

- Provide heavy-duty ground or power points of connections in vehicle circuits
- Bring power through bulkheads or other barriers between power and access points

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/Batterystuds](http://littelfuse.com/Batterystuds)

# BATTERY STUDS

## POWER DISTRIBUTION ACCESSORIES

### Ordering Information

PART NUMBERS	DESCRIPTION	PACKAGING	MAXIMUM CURRENT	BODY BY COLOR	STUD THREAD SIZE	CAP TYPE	Flat Washer Material	Split Lockwasher Material	Lockwasher Material
46210	Battery Jumper Stud, Positive	Bulk	6-36 VDC 285 AMPS	Red	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	No Lockwasher
46210-01	Battery Jumper Stud, Positive	Bulk	6-36 VDC 285 AMPS	Red	3/8 - 16	Red Cap	No Flat Washer	No Split Lockwasher	No Lockwasher
46210-02	Battery Jumper Stud, Positive	Bulk	6-36 VDC 285 AMPS	Red	3/8 - 16	Red Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46210-02-BX	Battery Jumper Stud, Positive, Boxed	Box	6-36 VDC 285 AMPS	Red	3/8 - 16	Red Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46210-03	Battery Jumper Stud, Negative	Bulk	6-36 VDC 285 AMPS	Black	3/8 - 16	Black Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46210-03-BX	Battery Jumper Stud, Negative, Boxed	Box	6-36 VDC 285 AMPS	Black	3/8 - 16	Black Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46210-04	Battery Jumper Stud, Negative	Bulk	6-36 VDC 285 AMPS	Black	3/8 - 16	Black Cap	No Flat Washer	No Split Lockwasher	No Lockwasher
46210-05	Battery Jumper Stud, Positive	Bulk	6-36 VDC 285 AMPS	Red	3/8 - 16	Red Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46210-08	Battery Jumper Stud, Negative	Bulk	6-36 VDC 285 AMPS	Black	3/8 - 16	Black Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46210-09	Battery Jumper Stud, Positive	Bulk	6-36 VDC 285 AMPS	Red	3/8 - 16	Red Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46210-10	Battery Jumper Stud, Negative	Bulk	6-36 VDC 285 AMPS	Black	3/8 - 16	Black Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46211-01	Feed Thru Stud, Negative	Bulk	6-36 VDC 260 AMPS	Black	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46211-01-BX	Feed Thru Stud, Negative, Boxed	Box	6-36 VDC 260 AMPS	Black	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46211-02	Feed Thru Stud, Negative	Bulk	6-36 VDC 250 AMPS	Black	½ - 20	No Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46211-03	Feed Thru Stud, Negative	Bulk	6-36 VDC 250 AMPS	Black	½ - 20	No Cap	Brass	Zinc Plated Steel	No Lockwasher
46211-04	Feed Thru Stud, Negative	Bulk	6-36 VDC 260 AMPS	Black	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	Bronze
46211-06	Feed Thru Stud, Negative	Bulk	6-36 VDC 260 AMPS	Black	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	No Lockwasher
46211-11	Feed Thru Stud, Negative	Bulk	6-36 VDC 260 AMPS	Black	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	No Lockwasher
46211-12	Feed Thru Stud, Negative	Bulk	6-36 VDC 260 AMPS	Black	M10 X 1.5	No Cap	No Flat Washer	No Split Lockwasher	No Lockwasher
46211-13	Feed Thru Stud, Positive	Bulk	6-36 VDC 260 AMPS	Red	M10 X 1.5	No Cap	No Flat Washer	No Split Lockwasher	No Lockwasher
46211-14	Feed Thru Stud, Negative	Bulk	6-36 VDC 260 AMPS	Black	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46211-R	Feed Thru Stud, Positive	Bulk	6-36 VDC 260 AMPS	Red	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
46211-R-BX	Feed Thru Stud, Positive, Boxed	Box	6-36 VDC 260 AMPS	Red	3/8 - 16	No Cap	No Flat Washer	No Split Lockwasher	Zinc Plated Steel
97846-A	Replacement Cap, Positive	Bulk	–	Red	–	–	–	–	–
97846-A-BX	Replacement Cap, Positive, Boxed	Box	–	Red	–	–	–	–	–
97846-B	Replacement Cap, Negative	Bulk	–	Black	–	–	–	–	–
97846-B-BX	Replacement Cap, Negative, Boxed	Box	–	Black	–	–	–	–	–