


# MIDI® FLEX SERIES

## 58V BOLT-DOWN FUSE HOLDER



04981038HXFC



04982001ZXFC

### Description

Thanks to its flexible cover, the MIDI® Flex Series 58V Bolt-Down Fuse Holder makes it simple to install up to a 200A MIDI® fuse. Its cover features 6 different positions for cable entry and accommodates large wire sizes and ring terminal stack up.

This bolt-down fuse holder has a dovetail feature on the sides that lets you connect multiple MIDI® Flex Series fuse holders. Busbars for multi-fuse applications are available (sold separately) so you can create a fused automotive power distribution block. MIDI® Flex Series fuse holders can also be combined with MEGA® Flex Series fuse holders (sold separately) for a high- and low-amperage solution.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/FLEX-MIDI](http://littelfuse.com/FLEX-MIDI)

### Ordering Information

PART NUMBER	DESCRIPTION	FUSE TYPE	MOUNTING METHOD	MAX CURRENT RATING	MAX VOLTAGE RATING
04981038-BP	58V Bolt-Down Fuse Holder - Blister Pack	MIDI Fuse	Bolt Down, M4 Mounting Hole	200A	58VDC
04981038HXFC	58V Bolt-Down Fuse Holder	MIDI Fuse	Bolt Down, M4 Mounting Hole	200A	58VDC
04982001ZXFC	58V Bolt-Down 2-Pole Fuse Holder	MIDI Fuse	Bolt Down, M4 Mounting Hole	200A	58VDC
84904	58V Bolt-Down Fuse Holder Base & Stud Assembly	-	Bolt Down, M4 Mounting Hole	-	-
84905	Flexible Fuse Holder Cover	-	-	-	-
882-267-002	2-Position Busbar for MIDI® Flex Series Fuse Holders	-	-	-	-
882-267-003	3-Position Busbar for MIDI® Flex Series Fuse Holders	-	-	-	-
882-267-004	4-Position Busbar for MIDI® Flex Series Fuse Holders	-	-	-	-
882-267-005	5-Position Busbar for MIDI® Flex Series Fuse Holders	-	-	-	-

### Specifications

<b>Current Rating Continuous:</b>	200A
<b>Fuse Type:</b>	MIDI® Fuse
<b>Flammability Rating:</b>	UL 94 V-0
<b>Input Terminals:</b>	M5 Stud
<b>Mounting Method:</b>	Bolt Down, M4 Mounting Hole
<b>Output Terminals:</b>	M5 STUD
<b>Max Voltage Rating:</b>	58VDC

### Applications

- Battery and Alternator Connections

### Features and Benefits

- Compatible with MIDI® bolt-down fuses up to 200A (sold separately unless indicated)
- Flexible cover allows cable entry at 6 different locations, simplifying installation and accommodating large wire sizes and ring terminal stack up
- Dovetail feature lets you connect multiple Flex Series fuse holders together to create a fused power distribution block (busbars for multi-fuse applications are sold separately)
- Slots molded into the base enable secure tie-wrap mounting
- Zinc-plated steel M5 studs and hex nuts
- Bolt-down fuse holder base features M4 mounting holes
- UL 94 V-0 flammability rating