

Specification Status: Released

Max Electrical Rating at 20°C

Operating Voltage: 60V_{DC}
Fault Voltage: 250V_{RMS}
Interrupt Current: 3A_{RMS}

Lead Material: Tin plated brass

Marking:

XX ——— Manufacturer's Mark

T13V ——— Part Identification




TABLE I. DIMENSIONS:

	A		B		C		D		E		F	
	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max	Min	Max
mm:	--	6.1	-	6.9	--	3.2	0.56	--	--	1.9	1.6	2.3
in:	--	(0.240)	--	(0.270)	--	(0.126)	(0.022)	--	--	(0.075)	(0.065)	(0.091)

TABLE II. PERFORMANCE RATINGS @ 20°C (unless otherwise noted):

I HOLD (A)	RESISTANCE (Ω)			TIME TO TRIP(s) @ 1A TYP	OPERATING TEMPERATURE (°C)		TRIPPED STATE POWER DISSIPATION (W) TYP
	R MIN	R MAX	R ₁ MAX*		MIN	MAX	
20°C	4.0	7.0	12.0	2.0	-40	85	1.5

*Maximum device resistance at 20°C measured 1 hour post trip or 24 hours post reflow.

Additional Ratings @ 20°C

Lightning Withstand: ITU at 1.5kV Storage Temperature: -40° to 85° C

Agency Recognition: UL, CSA, TUV
Reference Documents: PS300
Precedence: This specification takes precedence over documents referenced herein.
Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.
CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

ELV Compliant

Pb-Free



Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.