

JFGA7.E339112 - Fuses for Photovoltaic Systems Certified for Canada

Fuses for Photovoltaic Systems Certified for Canada

See General Information for Fuses for Photovoltaic Systems Certified for Canada

LITTELFUSE INC

SUITE 500
8755 W HIGGINS RD
CHICAGO, IL 60631 USA

E339112

Cat. No.	Interrupting Capacity		Rating			
	Volts	Amps	Volts	Amps		
	DC	AC	DC	AC		
SPFx, where x is replaced with 001-030 (ampere rating), may be followed by -R, may be followed by -SN	1000	—	20,000	1000	—	1-30
SPFx, where x is replaced with 001-020 (ampere rating), may be followed by -R, may be followed by -SN. Followed by CN	1000	—	20,000	1000	—	1-20
SPH 015	1050	—	20,000	1050	—	15
SPFx, where x is replaced with 025-030 (ampere rating), may be followed by -R, may be followed by -SN	1000	—	50,000	1000	—	25-30
SPFx, where x is replaced with 025-030 (ampere rating), followed by -E, may be followed by -R, may be followed by -SN	1000	—	50,000	1000	—	25-30
SPFx, where x is replaced with 025-030 (ampere rating), may be followed by -R, may be followed by -SN Followed by CN	1000	—	50,000	1000	—	25-30
SPFx, where x is replaced with 025-030 (ampere rating), followed by -E, may be followed by -R, may be followed by -SN Followed by CN	1000	—	50,000	1000	—	25-30
SPXCxxx, where XXX is replaced with 001-004 (ampere rating), may be followed by -SN, may be followed by -R	1500	—	15,000	1500	—	1-4
SPXVxxx, where XXX is replaced with 001-030 (ampere rating), may be followed by -SN	1500	—	30,000	1500	—	1-30
SPXVxxx, where XXX is replaced with 035-060 (ampere rating), may be followed by -SN	1500	—	50,000	1500	—	35-60
SPXVxxx-M, where XXX is replaced with 025-032 (ampere rating), may be followed by -SN	1500	—	50,000	1500	—	25-32
SPXVxxx, where XXX is replaced with 001-020 (ampere rating), may be followed by -SN Followed by CN	1500	—	30,000	1500	—	1-20

SPXVxxx-M, where XXX is replaced with 025-032 (ampere rating), may be followed by -SN Followed by CN	1500	—	50,000	1500	—	25-32
SPFJ	1000	—	20,000	1000	—	70-450
SPFJxxxL	1000	—	20,000	1000	—	125-200

Last Updated on 2021-02-08

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2021 UL LLC"