

4



3

2

1

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

SEE NOTE 2




NOTES:

1. ALL DIMENSIONS REFERENCE ONLY
2. AMP RATING
3. 12V CIRCUIT BREAKER

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF #519089 ADD 2 NEW PART PUT DRG ON SW FORMAT	5/4/2018	J. THOMAS



30419-30	30
30419-25	25
30419-20	20
30419-15	15
30419-10	10
30419-05	05
PART NO.	AMPS

INTERPRET DRAWING TO ANSI/ASME Y14.5-1994.

	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

DIMENSION; MM TOLERANCES UNLESS OTHERWISE SPECIFIED
ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100
TWO PLACES DECIMAL ± 0.20 ANGULAR $\pm 2^\circ$

	NAME	DATE
DRAWN	C. MILLER	05/04/18
CHECKED	J. THOMAS	09/04/18
	-	-
	-	-




Expertise Applied | Answers Delivered

TITLE

CIRCUIT BRKR, TYPE 2

FORM NO: CVP-PE40-0002 REV A

THIRD ANGLE PROJECTION



SIZE A	DWG. NO. 30419 CHART	REV. A
-----------	-------------------------	-----------

DO NOT SCALE DRAWING

SCALE 2:1

SHEET 1 OF 1

4

3

2

1