

00511200 & 00511300 CONNECTORS

13-Pole Plastic Body Plugs • 12V • ISO 11446



Specifications Overview

Voltage: 12V
Standards: ISO 1724

Web Resources

Download technical resources at:
littelfuse.com/connectors

Description

Provides a single connector for all the connections required in the old 7 p 12V system type N and S. The plug connects to the socket with a bayonet twist system to avoid accidental disconnection. The plugs are available both in the "traditional" version and in a new patented version, allowing faster assembly yet complying to the requirements of the norm. The new version has been equipped with a tool for fitting the insert which can also be used as a parking protection. Connectors are used for electrical connections between a vehicle and a trailer or caravan with 12V electrical system.

Features and Benefits

- Standards: Conforms to ISO 11446.
- Greater mechanical resistance.
- More reliable and safe electrical connection.
- The screw and crimp contacts version.
- Nickelplated brass contacts

Ordering Information

PART NUMBER			ISO	PIN MATERIAL NUMBER	TERMINAL TYPE
BULK 20 pcs.	BULK 100 pcs.	BULK 100 pcs. <input checked="" type="checkbox"/>			
00511200	00511290	00511299	11446	13 Nickel-plated brass	screw
00511100	00511190	00511199	11446	8 Nickel-plated brass	screw
00511160	-	-	11446	8 Nickel-plated brass	screw
00511300	00511390	00511399	11446	13 Nickel-plated brass	screw
00511000	-	-	11446	13 Nickel-plated brass	crimp
-	00510990	-	11446	8 Nickel-plated brass	crimp

PART NUMBER	BULK	IMG.	PLUG	DESCRIPTION OF ACCESSORIES
00603400 (10 pcs)	-	1	00511200 00511160 00511000 00511300	Rubber grommet with 1 cable outlets for-plugs Ø 12 mm
00603500 (10 pcs)	-	1	00511200 00511160 00511000 00511300	Rubber grommet with 1 cable outlets for-plugs Ø 15 mm
00603600 (10 pcs)	00603690 (500 pcs)	1	00511200 00511160 00511000 00511300	Rubber grommet with 1 cable outlets for-plugs Ø 17 mm
00603700 (10 pcs)	00603790 (500 pcs)	2	00511100 00510990	Rubber grommet with 2 cable outlets for-plugs Ø 10 mm
00604300 (10 pcs)	-	1	00511200 00511160 00511000 00511300	Green rubber grommet with 1 cable outlets for-plugs Ø 13,5 mm
00605100 (10 pcs)	-	2	00511100 00510990	Rubber grommet with 2 cable outlets for-plugs Ø 6,5 mm
00605600	00605690 (100 pcs)	3	00511200 00511100 00511000 00510990	Mounting tool for 13 pole plug
07990300	-	4	00511000 00510990	Hand crimping tool for pole

