



REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300044. INITIAL RELEASED. DSILVA.	4/21/2022	L.ARGIL

ART. NR.	DESCRIPTION	NOTE
178.6105.0001	FH2 BLOCK HOLDER PKG 100 PCS	-
178.6105.0002	FH2 BLOCK HOLDER BULK 1000 PCS	-

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U
3	-	HOUSING	1000	EAD
2	-	COVER	1000	EAD
1	-	DFK2 CONTACTS	2000	EAD

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)														
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400										ANGLE
±0.10	±0.10	±0.20	±0.30	±0.50										NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.	
PER CHNFPD20-008 PROCEDURE	● FIT/ FUNCTION CRITICAL CHARACTERISTICS
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
(ST)	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

	NAME	DATE
DRAWN	DSILVA	4/13/2022
CHECKED	-	-
	-	-
	-	-

FORM NO. CVP-PE40-0005 REV B	TITLE	
THIRD ANGLE PROJECTION	FH2 - BLOCKHOLDER, COMPLETE	
SIZE C	DWG. NO. OUTLINE	REV. A
DO NOT SCALE DRAWING	SCALE 2:1	SHEET 1 OF 1

1.	MATERIAL
2.	COVER: THERMOPLASTIC
3.	HOLDER: THERMOPLASTIC
	DFK CONTACTS: COPPER ALLOY