

Ø38.1 ± 0.18  
[Ø1.500 ± 0.007]

6.4 ± 0.08  
[0.250 ± 0.003]

10.3 ± 0.13  
[0.406 ± 0.005]

65.1 ± 1.57  
[2.562 ± 0.062]


88.9 ± 1.57  
[3.500 ± 0.062]

49.2 ± 1.57  
[1.938 ± 0.062]  
31.8  
[1.250]

25.3 ± 0.25  
[0.995 ± 0.010]

REVISION

REV	DATE	DESCRIPTION
A	6/27/23	526651GCP - RELEASE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			
MATL SPEC			FINISH	
DRW JMoler	DATE 6/19/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994				
3RD ANGLE PROJECTION				
TITLE				
L15S 500-1000A OUTLINE				
 <b>Littelfuse®</b> CHICAGO, ILLINOIS 60631		REVISION A	DRWG NO. OL-L15S1000	SHEET 1 OF 1