

4

3



2

1

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF #524724 INITIAL RELEASED. D.SILVA.	1/25/2022	L.ARGIL



NOTES:

1. ASSOCIATED 3D CAD FILE DEFINE ALL NON DIMENSIONED FEATURES.
2. THIS IN-LINE FUSEHOLDER IS DESIGNED FOR TURNS ONE FUSE SLOT INTO TWO.
3. INSTALLATION RATING UP TO 10AMPS.
4. BUTT SPLICE CONNECTOR PULL OUT FORCE 15KGF MIN.



NO.	COMPONENT NO.	COMPONENT NAME	QTY	U
-----	---------------	----------------	-----	---

TOLERANCES OTHERWISE SPECIFIED (REF. ISO 2768-mK)

.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400	ANGLE
±0.10	±0.10	±0.20	±0.30	±0.50	NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

●	FIT/ FUNCTION CRITICAL CHARACTERISTICS
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

	NAME	DATE	<div>Littelfuse</div> <div>Expertise Applied Answers Delivered</div>			
DRAWN	D.SILVA	1/4/2022				
CHECKED	-	-				
	-	-				
	-	-				
FORM NO: CVP-PE40-0001 REV B			TITLE HOLDER LP MINI ADD-A-CIRCUIT 10A			
THIRD ANGLE PROJECTION						
			SIZE B	DWG. NO. OUTLINE	OL-FHLM0200Z	REV A
DO NOT SCALE DRAWING			SCALE 1:2		SHEET 1 OF 1	