









FEMALE TERMINAL FOR MINI FUSE					LTR	DATE	REVISION	CHK	APD
CABLE SIZE mm ²	FEMALE TERMINAL (DELPHI 280 SEALED)	CABLE DIA	CABLE SEAL (DELPHI 280 METRI-PACK REEL/LOOSE)	COLOR	A	09/23/11	503307ERA - SEE ERN RD		
0.50 - 0.35	12084201	1.70 - 1.29	12034365/15324983	DARK RED	B	01/05/13	507139ECA - SEE ECO FYUE		
1.0 - 0.50	12077411	2.15 - 1.60	12089444/15324985	PURPLE	C	05/30/13	508391ECA - SEE ECO FYUE		
3.0 - 2.0	12129493	2.42 - 2.03	12041352/15324984	TAN	D	24/Mar/17	516851ECC - CHANGE BASE FYUE		
3.0	12077413	2.85 - 2.03	12015284/15324982	GREEN					
		3.49 - 2.81	12015359/15324980	GRAY					
		4.30 - 3.45	12015360/15324981	BLUE					
		CAVITY PLUG	12010300	GREEN					



- NOTE:
- MATERIAL:
BASE/COVER: NYLON66 - BLACK
SEAL: 30 DURO SILICONE (GREEN)
 - TORQUE RATING: 5.5-6.5 Nm USING M6 BOLT & LOCK WASHER
 - MAX. TOTAL CURRENT @ 23°C IS 100A
MAX. TOTAL CURRENT @ 85°C IS 70A.
ALL FUSE MUST NOT EXCEED 70% OF RATED CURRENT.
 - OPERATING & STORAGE TEMPERATURE: -40°C TO 85°C
 - ASSEMBLY MUST PASS IP67 IEC60529 TESTS.
 - COVER MUST WITHSTAND A PULL FORCE OF 15-30N WHEN INSTALLED WITH SEAL AND BASE.
 - TERMINAL RETENTION MUST MEET REQUIREMENTS OF
USCAR 2 SECTION 5.4.1.3 USING PROPER DELPHI METRI-PACK TERMINALS (SEALED/TANGLESS):
TERMINAL INSERTION FORCE: 30N MAX. (15N MAX. FOR WIRE SIZE <=1mm²)
TERMINAL EXTRACTION FORCE: 60N MIN.
TERMINAL EXTRACTION FORCE WITH TPA INSTALLED: 90N MIN.
 - PARTS ARE SHIPPED WITH THE BASE WITH COVER AND SEAL INSTALLED.
 - TO BE USED WITH FUSE PULLER 00970032Z.
 - HOLDER MEETS L/F VALIDATION TEST SPEC. VS-00510.
 - TO BE USED WITH DELPHI METRI-PACK TERMINALS AND SEALS.
 - THE SEAL SHOULD NOT BE REMOVED NOR DISPLACED DURING TRANSPORT UNTIL IT IS USED FOR PRODUCTION.

3	868-965	BASE		
2	901-106	COVER SEAL		
1	873-032	COVER		
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS () ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
⬢ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
				
COPIES TO	MATL SPEC			
REFER TO NOTE 1				
1 9 18	FINISH			
2 10 19				
3 12 20				
4 13 21	DRW	RLDJ	DATE	05/05/11
5 14 23			SCALE	1:1
6 15 33	CHK	DATE		SUPER DR
7 16 43			DATE	
8 17 53	APPD	DATE		FINSH GOOD WT
GRAMS/PIECE				
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)				
DIMENSION	0.5 - 3	OVER 3 - 6	OVER 6 - 30	OVER 30 - 120
TOLERANCE	±0.1	±0.1	±0.2	±0.3
UP TO 400				
3RD ANGLE PROJECTION	TITLE 18 WAY FUSE HOLDER ASSY (HWB18 ASSY)			
				
		REVISION	DRWG. NO.	
LIPA CITY, BATANGAS, PHILIPPINES		D	OL-PDM31003ZXM	

METRIC
ASSEMBLY

Littelfuse
LIPA CITY, BATANGAS, PHILIPPINES

REVISION D
DRAWG. NO. OL-PDM31003ZXM

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED