






MATERIAL:
BODY-GREY GLASS FILLED NYLON (UL94VO)
CLIP-BeCu, TIN PLATE FINISH

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

○	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

COPIES TO			MATL SPEC		FINISH	
1	9	18	DRW	KAM	DATE	1/21/98
2	10	19			SCALE	2:1
3	12	20	CHK		DATE	SUPER DRW
4	13	21				
5	14	23	APPD		DATE	RAW STK WT
6	15	33	TOLERANCE UNLESS OTHERWISE SPECIFIED			
7	16	43				
8	17	53				
			TWO PLACE DEC		±.01	FRACT
			THREE PLACE DEC		±.005	ANG

MINIFUSE VERTICAL MOUNT
PCB FUSEHOLDER



OUTLINE

01530016Z

DES PLAINES, ILLINOIS 60016

DATE	RAW STK WT
ANCE UNLESS OTHERWISE SPECIFIED	
E DEC ± 0.01	FRAC
ACE DEC ± 0.005	ANG
NIFUSE VERTICAL MOUNT	
FUSEHOLDER	R
OUTLINE	
01530016Z	

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED