






- NOTES:
1. DRAWING SHOWN WITH FUSES INSTALLED, FUSE LOADING CONFIGURATION DEPENDANT
 2. ALL STUDS TO BE STAINLESS STEEL WITH ROLLED THREADS
 3. ALL BUS BARS TO BE TIN PLATED COPPER
 4. WEIGHT: 0.8 LB
 5. RECCOMENDED TORQUE VALUES:
 1. MIDI FUSES - 3 N-m(27 IN-LB)
 2. RECOMMENDED INPUT TERMINAL STUD NUT TORQUE - 20 N-m(15 FT-LB)
 3. RECOMMENDED OUTPUT TERMINAL STUD NUT TORQUE - 20 N-m(15 FT-LB)
 6. DRAWING SHOWN WITHOUT OPTIONAL LABEL, LABEL LOCATED ON OUTSIDE OF COVER
 7. INCLUDED HARDWARE (TO BE INSTALLED AT LESS THAN 300 RPM);
 4. M8x1.25 18-8 STAINLESS STEEL 4X
 8. CONNECTOR HOUSING: FCI APEX 2.8MM FEMALE 4-WAY
FCI P/N: 54200409
 9. MATERIAL:
HOUSING: GLASS FILLED NYLON 94V-0 COVER: PC 94V-0
 10. MIN/MAX TEMPERATURE RATING: OPESTRATIONAL: -40C~100C NON-OPERATIONAL: -55C~125C
 11. MAX CURRENT INPUT: 350 AMPS



DIMENSIONS ARE IN MM.				Littelfuse			
DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI / ASME Y14.5M-1994				805 W. Orchard DR., Ste. 6, Bellingham, WA 98225 Phone (360)738-9010 Fax (360)738-0372			
THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.				Power Distribution Module w/cover			
THIRD ANGLE PROJECTION				SIZE	DWG. NO.	REV.	
				C	OL-880073	A	
SCALE 1:2				SHEET 1 OF 1			