






REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	ECN# 00024	TY	1/14/2020
	B	ECO #523271 - ADD SPECIFICATION NOTE RELATED TO ADD STICK LABEL & WHITE BOX PACKAGING	2/10/2021	S CASTILLO



WIRING DIAGRAM LABEL

- NOTES:
1. ALL STEEL PARTS ARE PLATED.
 2. ALL DIMENSIONS ARE REFERENCE ONLY.
 3. PACK SOLENOID IN WHITE BOX CA-531 AND STICK LABEL 663 (PROP. 65) IN BOX.

MM
[INCH]

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.									
	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL								
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL								
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE								
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS								
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE								
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF.ISO2768-M) FOR METAL, REF.SPI PLASTICS									
DIMENSION MM	UP TO 0.5 - 3	OVER 3 - 6	OVER 6 - 30	UP TO 30 - 120	OVER 120 - 400	UP TO 0.1	UP TO 0.2	UP TO 0.3	UP TO 0.5
TOLERANCES	±0.1	±0.1	±0.2	±0.3	±0.5	±0.1	±0.2	±0.3	±0.5*
DRAWN	NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered						
CHECKED	TY	09/14/99							
-	-	-							
-	-	-							
FORM NO: CVP-PE40-0005 REV A			TITLE						
THIRD ANGLE PROJECTION			SOLID STATE SOLENOID						
			SIZE C	DWG. NO. 48785				REV. B	
DO NOT SCALE DRAWING			SCALE 1:1				SHEET 1 OF 1		