



METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
 CPK	DENOTES CRITICAL CHARACTERISTICS.			
	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

2.0mm MS PLATE									
MATL SPEC									
FINISH									
ZINC CHROMATE PLATED (t = 3-8 microns)									
DRW FYUE DATE 21/Jun/16 SCALE 1:1									
CHK DATE SUPER DR									
APPD DATE FINSH GOOD WT									
GRAMS/PIECE									
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)									
DIMENSION 0.5 - 3 UP TO 3 OVER 6 - 30 UP TO 30 OVER 120 - 400 UP TO 120 OVER 400									
TOLERANCE ±0.1 ±0.1 ±0.2 ±0.3 ±0.5									
3RD ANGLE PROJECTION									
TITLE METAL BRACKET (for HWB18)									
									
LITTLEFUSE® LIPA CITY, BATANGAS, PHILIPPINES									
REVISION DRWG. NO. 868-066									
A									
OUTLINE									