




NOTES:

1. MAX. RATING, 20 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	FINISH	
1	9 18	DRW PJM	DATE 10/15/01	SCALE 1:1
2	10 19			
3	12 20	CHK	DATE	SUPER DRW
4	13 21			
5	14 23	APPD	DATE	RAW STK WT LBS/M
6	15 33			
7	16 43			
8	17 53			
TITLE		TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.01 THREE PLACE DEC ±.005 ANGULAR ±1°		
		MINIFUSE HOLDER, IN LINE		
 DES PLAINES, ILLINOIS 60016		DRAWING NO.		SERIES OUTLINE
		A		01530029Z
LTR		REVISION		
A	60683 - RELEASE 10/15/01 PJM			
	CHK	APD		

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

9 DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

STANDARDIZATION OF INSPECTION PROCEDURE FOR MEASUREMENT OF PROCESS PERFORMANCE. PROCEDURE TO BE DEFINED IN NATLFUSE INSPECTION INSTRUCTIONS.

DEFINITE CP DIMENSIONS.—MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

[illegible]