



REV.		DESCRIPTION	REVISIONS		
A		FIRST ISSUE OF OUTLINE DRAWING	DATE	DESIGNED	APPROVED
			02-July-2020	Gasparini	Tinto



MECHANICAL CHARACTERISTICS




- Numbers of electrical and mechanical operations: 100.000
- Tightening torque nuts M10/M12: 20 ± 2 Nm
- Tightening torque nuts M5/M6: 1.6 ± 0.4 Nm

ELECTRICAL CHARACTERISTICS

- Nominal voltage range: 12 + 24 V
- Maximum continuous current on main contacts: 250A
- Maximum short time current on main contacts: 2000A at 23°C for 30sec

PRESCRIPTIONS


- (*): Marking of date of manufacturing according to standard LITTELFUSE
- (\$): To apply the label indifferently on one box side or the opposite
- (£): Cap for M5 pos. coil pin identification, to remove during TGC installation on vehicle
- It is prudent to fixing the product to the structure using M8 screws and flat washers under the head



Vista da A

SAP drawing number:

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3 ±0,2	>3 6 ±0,3	>6 30 ±0,5	>30 120 ±0,8	>120 400 ±1,2	>400 1000 ±2	>1000 2000 ±3
angle (for range of lengths)						
up to 10 ±1°30'		>10 50 ±1°		>50 120 ±0°30'		>120 400 ±0°15'
● FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL						
<S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL						
CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE						
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS						
CP DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE						
NAME		DATE				
DRAWN		L. Dal Molin		20/05/2019		
CHECKED		-		-		
-		-		-		
-		-		-		
						
		Littelfuse®				
		Expertise Applied Answers Delivered				
FORM NO. CVP-PE40-0013 REV A		TITLE				
FIRST ANGLE PROJECTION		REMOTE CONTROL SWITCH TGC				
		12V(Positive or negative				
		disc)connection) OL-08094900				
DO NOT SCALE DRAWING		SCALE 1:1		SHEET 1 OF 1		