





LTR	DATE	REVISION	CHK	APD
A	04/24/15	GCF511823GCA-NEW RELEASE FYUE		



-										
-										
-										
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M						
BILL OF MATERIAL										
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES										
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.										
⊙	DENOTES CRITICAL CHARACTERISTICS.									
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE									
⊙ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS									
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE									
COPIES TO		MATL SPEC COVER: THERMOPLAST HOLDER: THERMOPLAST DFK2 CONTACTS: COPPER ALLOY								
1	9	18	FINISH							
2	10	19	-							
3	12	20								
4	13	21	DRW	FYUE	DATE	04/24/15	SCALE	4:1		
5	14	23	CHK		DATE		SUPER DR			
6	15	33	APPD		DATE		FINSH GOOD WT			
7	16	43			GRAMS/PIECE					
8	17	53								
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)										
DIMENSION	0.5 - 3		UP TO 3	OVER 3 - 6	UP TO 6	OVER 6 - 30	UP TO 30	OVER 30 - 120	UP TO 120	OVER 120 - 400
TOLERANCE	±0.1		±0.1	±0.1	±0.2	±0.3	±0.3	±0.5	±0.5	±0.5
3RD ANGLE PROJECTION		TITLE								
		FH2 HOLDER WITH BLADE TERMINAL								
		REVISION		DRWG. NO.		OUTLINE				
		A		178.6105.1002						
CHICAGO, IL 773-628-1000										

METRIC
ASSEMBLY



CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)