



### DSTF40100C



#### Pin out



#### Description

Littelfuse DST series Ultra Low  $V_F$  Schottky Barrier Rectifier is designed to meet the general requirements of commercial and industry applications by providing high temperature, low leakage and lower  $V_F$  products.

It is suitable for high frequency switching mode power supply, free-wheeling diodes and polarity protection diodes.

#### Features

- Ultra low forward voltage drop
- High frequency operation
- High junction temperature capability
- Guard ring for enhanced ruggedness and long term reliability
- Common cathode configuration in ITO-220AB package

#### Applications

- Switching mode power supply
- DC/DC converters
- Free-Wheeling diodes
- Polarity Protection Diodes

#### Maximum Ratings

| Parameters                                            | Symbol      | Test Conditions                                                    | Max                               | Unit |
|-------------------------------------------------------|-------------|--------------------------------------------------------------------|-----------------------------------|------|
| Peak Inverse Voltage                                  | $V_{RWM}$   | -                                                                  | 100                               | V    |
| Average Forward Current                               | $I_{F(AV)}$ | 50% duty cycle @ $T_c = 85^\circ\text{C}$<br>rectangular wave form | 20 (per leg)<br>40 (total device) | A    |
| Peak One Cycle Non-Repetitive Surge Current (per leg) | $I_{FSM}$   | 8.3 ms, half Sine pulse                                            | 300                               | A    |

#### Electrical Characteristics


| Parameters                                                                                  | Symbol    | Test Conditions                                                                                         | Typ   | Max  | Unit |
|---------------------------------------------------------------------------------------------|-----------|---------------------------------------------------------------------------------------------------------|-------|------|------|
| Forward Voltage Drop (per leg) *                                                            | $V_{F1}$  | @5A, Pulse, $T_J = 25^\circ\text{C}$                                                                    | 0.47  | -    | V    |
|                                                                                             |           | @10A, Pulse, $T_J = 25^\circ\text{C}$                                                                   | 0.54  | -    |      |
|                                                                                             |           | @20A, Pulse, $T_J = 25^\circ\text{C}$                                                                   | 0.68  | 0.75 |      |
|                                                                                             | $V_{F2}$  | @5A, Pulse, $T_J = 125^\circ\text{C}$                                                                   | 0.38  | -    |      |
|                                                                                             |           | @10A, Pulse, $T_J = 125^\circ\text{C}$                                                                  | 0.51  | -    |      |
|                                                                                             |           | @20A, Pulse, $T_J = 125^\circ\text{C}$                                                                  | 0.64  | 0.70 |      |
| Reverse Current (per leg) *                                                                 | $I_{R1}$  | @ $V_R = 70\text{V}$ , $T_J = 25^\circ\text{C}$                                                         | 0.012 | -    | mA   |
|                                                                                             |           | @ $V_R = 100\text{V}$ , $T_J = 25^\circ\text{C}$                                                        | 0.030 | 1    |      |
|                                                                                             | $I_{R2}$  | @ $V_R = 70\text{V}$ , $T_J = 125^\circ\text{C}$                                                        | 10    | -    |      |
|                                                                                             |           | @ $V_R = 100\text{V}$ , $T_J = 125^\circ\text{C}$                                                       | 15    | 75   |      |
| Junction Capacitance (per leg)                                                              | $C_T$     | @ $V_R = 5\text{V}$ , $T_c = 25^\circ\text{C}$ , $f_{SI} = 1\text{MHz}$                                 | 845   | -    | pF   |
| RSM Isolation Voltage<br>( $t = 1.0$ second, R. H. $< 30\%$ ,<br>$T_A = 25^\circ\text{C}$ ) | $V_{ISO}$ | Clip mounting, the epoxy body away from the heatsink edge by more than 0.110" along the lead direction. | -     | 4500 | V    |
|                                                                                             |           | Clip mounting, the epoxy body is inside the heatsink.                                                   | -     | 3500 |      |
|                                                                                             |           | Screw mounting, the epoxy body is inside the heatsink.                                                  | -     | 1500 |      |

\* Pulse Width  $< 300\mu\text{s}$ , Duty Cycle  $< 2\%$


**Thermal-Mechanical Specifications**

| Parameters                                    | Symbol     | Test Conditions | Max         | Unit |
|-----------------------------------------------|------------|-----------------|-------------|------|
| Junction Temperature                          | $T_J$      |                 | -55 to +150 | °C   |
| Storage Temperature                           | $T_{stg}$  |                 | -55 to +150 | °C   |
| Thermal Resistance Junction to Case (per leg) | $R_{thJC}$ | DC operation    | 4.0         | °C/W |
| Approximate Weight                            | wt         |                 | 2           | g    |
| Case Style                                    | ITO-220AB  |                 |             |      |


**Figure 1: Typical Forward Characteristics**




**Figure 2: Typical Reverse Characteristics**



**Figure 3: Typical Junction Capacitance**



**Dimensions- ITO-220AB**



| Symbol     | Millimeters |       |       |
|------------|-------------|-------|-------|
|            | Min         | Typ   | Max   |
| <b>A</b>   | 4.30        | 4.50  | 4.70  |
| <b>A1</b>  | 1.10        | 1.30  | 1.50  |
| <b>A2</b>  | 2.80        | 3.00  | 3.20  |
| <b>A3</b>  | 2.50        | 2.70  | 2.90  |
| <b>b</b>   | 0.50        | 0.60  | 0.75  |
| <b>b1</b>  | 1.10        | 1.20  | 1.35  |
| <b>b2</b>  | 1.50        | 1.60  | 1.75  |
| <b>b3</b>  | 1.20        | 1.30  | 1.45  |
| <b>b4</b>  | 1.60        | 1.70  | 1.85  |
| <b>c</b>   | 0.55        | 0.60  | 0.75  |
| <b>D</b>   | 14.80       | 15.00 | 15.20 |
| <b>E</b>   | 9.96        | 10.16 | 10.36 |
| <b>e</b>   |             | 2.55  |       |
| <b>e1</b>  |             | 5.10  |       |
| <b>H1</b>  | 6.50        | 6.70  | 6.90  |
| <b>L</b>   | 12.70       | 13.20 | 13.70 |
| <b>L1</b>  | 1.60        | 1.80  | 2.00  |
| <b>L2</b>  | 0.80        | 1.00  | 1.20  |
| <b>L3</b>  | 0.60        | 0.80  | 1.00  |
| <b>ØP1</b> | 3.30        | 3.50  | 3.70  |
| <b>ØP2</b> | 2.99        | 3.19  | 3.39  |
| <b>Q</b>   | 2.50        | 2.70  | 2.90  |
| <b>Ø1</b>  |             | 5°    |       |
| <b>Ø2</b>  |             | 4°    |       |
| <b>Ø3</b>  |             | 10°   |       |
| <b>Ø4</b>  |             | 5°    |       |
| <b>Ø5</b>  |             | 5°    |       |


**Packing Options**

| Part Number | Marking    | Packing Mode | M.O.Q |
|-------------|------------|--------------|-------|
| DSTF40100C  | DSTF40100C | 50pcs / Tube | 1000  |

**Tube Specification**



**Part Numbering and Marking System**



DST = Device Type  
 F = Package type  
 40 = Forward Current (40A)  
 100 = Reverse Voltage (100V)  
 C = Configuration  
 LF = Littelfuse  
 YY = Year  
 WW = Week  
 L = Lot Number