



Three Phase Half Controlled Rectifier Bridge, B6HK

$$I_{dAVM} = 110/167 \text{ A}$$

$$V_{RRM} = 1200-1600 \text{ V}$$

V_{RSM} V_{DSM} V	V_{RRM} V_{DRM} V	Type
1300 1700	1200 1600	VVZ 110-12io7 VVZ 175-12io7 VVZ 175-16io7



Symbol	Test Conditions	Maximum Ratings		
		VVZ 110	VVZ 175	
I_{dAV} I_{FRMS}, I_{TRMS}	$T_C = 85^{\circ}C$; module per leg	110 58	167 89	A A
I_{FSM}, I_{TSM}	$T_{VJ} = 45^{\circ}C$; $t = 10\text{ ms}$ (50 Hz), sine	1150	1500	A
	$V_R = 0$ $t = 8.3\text{ ms}$ (60 Hz), sine	1230	1600	A
	$T_{VJ} = T_{VJM}$ $t = 10\text{ ms}$ (50 Hz), sine	1000	1350	A
	$V_R = 0$ $t = 8.3\text{ ms}$ (60 Hz), sine	1070	1450	A
I^2t	$T_{VJ} = 45^{\circ}C$ $t = 10\text{ ms}$ (50 Hz), sine	6600	11200	A ² s
	$V_R = 0$ $t = 8.3\text{ ms}$ (60 Hz), sine	6280	10750	A ² s
	$T_{VJ} = T_{VJM}$ $t = 10\text{ ms}$ (50 Hz), sine	5000	9100	A ² s
	$V_R = 0$ $t = 8.3\text{ ms}$ (60 Hz), sine	4750	8830	A ² s
$(di/dt)_{cr}$	$T_{VJ} = T_{VJM}$ repetitive, $I_T = 50\text{ A}$ $f = 400\text{ Hz}$, $t_p = 200\text{ }\mu s$ $V_D = 2/3\text{ }V_{DRM}$	150		A/ μs
	$I_G = 0.3\text{ A}$, non repetitive, $di_G/dt = 0.3\text{ A}/\mu s$, $I_T = 1/3 \cdot I_{dAV}$	500		A/ μs
$(dv/dt)_{cr}$	$T_{VJ} = T_{VJM}$; $V_{DR} = 2/3\text{ }V_{DRM}$ $R_{GK} = \infty$; method 1 (linear voltage rise)	1000		V/ μs
V_{RGM}		10		V
P_{GM}	$T_{VJ} = T_{VJM}$ $t_p = 30\text{ }\mu s$	≤ 10		W
	$I_T = I_{TAVM}$ $t_p = 500\text{ }\mu s$	≤ 5		W
	$t_p = 10\text{ ms}$	≤ 1		W
		0.5		W
P_{GAVM}				
T_{VJ}		-40...+125		$^{\circ}C$
T_{VJM}		125		$^{\circ}C$
T_{stg}		-40...+125		$^{\circ}C$
V_{ISOL}	50/60 Hz, RMS $t = 1\text{ min}$	2500		V~
	$I_{ISOL} \leq 1\text{ mA}$ $t = 1\text{ s}$	3000		V~
M_d	Mounting torque (M6)	5±15 %		Nm
	Terminal connection torque (M6)	5±15 %		Nm
Weight	typ.	300		g

Data according to IEC 60747 and refer to a single thyristor/diode unless otherwise stated.

Features

- Package with screw terminals
- Isolation voltage 3000 V~
- Planar passivated chips
- UL registered E72873

Applications

- Input rectifier for PWM converter
- Input rectifier for switch mode power supplies (SMPS)
- Softstart capacitor charging

Advantages

- Easy to mount with two screws
- Space and weight savings
- Improved temperature and power cycling

Symbol	Test Conditions	Characteristic Values		
		VVZ 110	VVZ 175	
I_R, I_D	$V_R = V_{RRM}; V_D = V_{DRM}$ $T_{VJ} = T_{VJM}$ $T_{VJ} = 25^\circ\text{C}$	≤ 5 ≤ 0.3		mA mA
V_F, V_T	$I_F, I_T = 200 \text{ A}, T_{VJ} = 25^\circ\text{C}$	≤ 1.75	1.57	V
V_{T0}	For power-loss calculations only	0.85	0.85	V
r_T	$(T_{VJ} = 125^\circ\text{C})$	6	3.5	m Ω
V_{GT}	$V_D = 6 \text{ V};$ $T_{VJ} = 25^\circ\text{C}$ $T_{VJ} = -40^\circ\text{C}$	$\leq$ $\leq$	1.5 1.6	V V
I_{GT}	$V_D = 6 \text{ V};$ $T_{VJ} = 25^\circ\text{C}$ $T_{VJ} = -40^\circ\text{C}$	$\leq$ $\leq$	100 200	mA mA
V_{GD}	$T_{VJ} = T_{VJM};$ $T_{VJ} = T_{VJM};$	$\leq$ $\leq$	0.2 5	V mA
I_{GD}	$V_D = \frac{2}{3} V_{DRM}$ $V_D = \frac{2}{3} V_{DRM}$			
I_L	$I_G = 0.3 \text{ A}; t_g = 30 \mu\text{s}$ $di_G/dt = 0.3 \text{ A}/\mu\text{s}$ $T_{VJ} = 25^\circ\text{C}$	$\leq$	450	mA
I_H	$T_{VJ} = 25^\circ\text{C}; V_D = 6 \text{ V}; R_{GK} = \infty$	$\leq$	200	mA
t_{gd}	$T_{VJ} = 25^\circ\text{C}; V_D = \frac{1}{2} V_{DRM}$ $I_G = 0.3 \text{ A}; di_G/dt = 0.3 \text{ A}/\mu\text{s}$	$\leq$	2	μs
R_{thJC}	per thyristor (diode); DC current per module	0.65 0.108	0.46 0.077	K/W K/W
R_{thJH}	per thyristor (diode); DC current per module	0.8 0.133	0.55 0.092	K/W K/W
d_s	Creeping distance on surface		10	mm
d_A	Creepage distance in air		9.4	mm
a	Max. allowable acceleration		50	m/s ²




Fig. 1 Gate trigger characteristics




Fig. 2 DC output current at case temperature

Dimensions in mm (1 mm = 0.0394")





Fig. 3 Surge overload current
 I_{FSM} : Crest value, t : duration




Fig. 4 Transient thermal impedance
junction to case (per leg)



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.