



CoolMOS™¹⁾ Power MOSFET

ISOPLUS™ - electrically isolated surface to heatsink
Surface Mount Power Device

$$\begin{aligned} V_{DSS} &= 600 \text{ V} \\ I_{D25} &= 50 \text{ A} \\ R_{DS(on) \text{ max}} &= 45 \text{ m}\Omega \end{aligned}$$

Preliminary data



RL E72873

MOSFET T							
Symbol	Conditions	Maximum Ratings					
V _{DSS}	T _{VJ} = 25°C to 150°C	600		V			
V _{GS}		±20		V			
I _{D25}	T _C = 25°C	50		A			
I _{D80}	T _C = 80°C	38		A			
E _{AS} E _{AR}	single pulse repetitive	} I _D = 11 A; T _C = 25°C	1950	mJ			
			3	mJ			
dV/dt	MOSFET dV/dt ruggedness V _{DS} = 0...480 V	50		V/ns			
Symbol	Conditions	Characteristic Values					
(T _{VJ} = 25°C, unless otherwise specified)							
		min.	typ.	max.			
R _{DSon}	I _D = 44 A; V _{GS} = 10 V		40	45	mΩ		
V _{GS(th)}	I _D = 3 mA; V _{DS} = V _{GS}	2.5	3	3.5	V		
I _{DSS}	V _{DS} = V _{DSS} ; V _{GS} = 0 V; T _{VJ} = 25°C T _{VJ} = 125°C		50	10	μA μA		
I _{GSS}	V _{DS} = 0 V; V _{GS} = ± 20 V			100	nA		
t _{d(on)} t _r t _{d(off)} t _f E _{on} E _{off} E _{rec}	Inductive switching boost mode with diode D V _{DS} = 380 V; I _D = 30 A V _{GS} = 10 V; R _G = 33 Ω		80 40 750 40 1.3 0.45 0.35		ns ns ns ns mJ mJ mJ		
C _{iss} C _{oss}		} V _{GS} = 0 V; V _{DS} = 100 V; f = 1 MHz		6800 320		pF pF	
Q _g Q _{gs} Q _{gd}			} V _{DS} = 400 V; I _D = 44 A V _{GS} = 10 V; R _G = 3.3 Ω		150 35 50	190	nC nC nC
R _{thJC} R _{thJH}		with heatsink compound (IXYS test setup)			tbd	0.4 tbd	K/W K/W

Features

- **Fast CoolMOS™¹⁾** power MOSFET 4th generation
 - high blocking capability
 - lowest resistance
 - avalanche rated for unclamped inductive switching (UIS)
 - low thermal resistance due to reduced chip thickness
- **Package**
 - isolated surface to heatsink
 - low coupling capacity between pins and heatsink
 - PCB space saving
 - enlarged creepage towards heatsink
 - application friendly pinout
 - low inductive current path
 - high reliability

Applications

- Buck / boost chopper
- Optimized for boost configuration
- PFC stage

¹⁾ CoolMOS™ is a trademark of Infineon Technologies AG.

Source-Drain Diode of MOSFET T

Symbol	Conditions	Maximum Ratings			
I _{S25}	T _C = 25°C			50	A
I _{S80}	T _C = 80°C			38	A
Symbol	Conditions	Characteristic Values			
(T _{VJ} = 25°C, unless otherwise specified)					
		min.	typ.	max.	
V _{SD}	I _F = 44 A; V _{GS} = 0 V		0.9	1.0	V
t _{rr}	I _F = 44 A; -di _F /dt = 100 A/μs; V _R = 400 V		600		ns
Q _{RM}			17		μC
I _{RM}			60		A

Diode D


Symbol	Conditions	Maximum Ratings			
I _{F25}	T _C = 25°C; DC	96	A		
I _{F80}	T _C = 80°C; DC	61	A		
Symbol	Conditions	Characteristic Values			
(T _{VJ} = 25°C, unless otherwise specified)					
		min.	typ.	max.	
V _{RRM}	T _{VJ} = 25°C			600	V
V _F	I _F = 25 A	T _{VJ} = 25°C T _{VJ} = 125°C	1.2 1.3	1.4	V
I _R	V _R = V _{RRM}	T _{VJ} = 25°C T _{VJ} = 125°C		150	μA mA
I _{RM}	I _F = 30 A; V _R = 350 V -di/dt = 240 A/μs	T _{VJ} = 100°C	10		A
t _{rr}	I _F = 1 A; V _R = 30 V -di/dt = 100 A/μs	T _{VJ} = 100°C	35	50	ns
R _{thJC} R _{thJH}	per diode with heatsink compound (IXYS test setup)		tbd	0.7	K/W k/W

Component

Symbol	Conditions	Maximum Ratings			
T_{VJ}		-55...+150			°C
T_{stg}		-55...+125			°C
V_{ISOL}	$I_{ISOL} \leq 1\text{ mA}; 50/60\text{ Hz}$	2500			V~
F_C	mounting force	40 ... 130			N
Symbol	Conditions	Characteristic Values			
		min.	typ.	max.	
C_P	coupling capacity between shorted pins and backside metal		90		pF
d_S, d_A	pin - pin	1.65			mm
d_S, d_A	pin - backside metal	4			mm
CTI		400			
Weight			8		g



Equivalent Circuits for Simulation

Conduction



Boost Diode (typ. at $T_J = 125^\circ\text{C}$)
 $V_0 = tbd\text{ V}; R_0 = tbd\text{ m}\Omega$

Ordering	Part Number	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	MKE38RK600DFELB-TRR	MKE38RK600DFELB	Tape & Reel	200	510479
	MKE38RK600DFELB	MKE38RK600DFELB	Blister	45	510231



The Data Matrix Code contains the following information in 36 digits:

Digits 1 through 20: part number
 21 to 25: date code (YYWWA)
 26 to 31: assembly lot code
 32: reserved for special information
 33 to 36: may be used for subsequent module numbering within the assembly lot




Fig.1 Drain source breakdown voltage versus temperature T_{VJ}




Fig. 2 Typ. transfer characteristics




Fig. 3 Typical output characteristics




Fig. 4 Typical output characteristics




Fig.5 Drain source on-state resistance $R_{DS(on)}$ vs. junction temperature T_{VJ}




Fig. 6 Drain source on-state resistance, $R_{DS(on)}$ versus I_D




Fig. 7 Typ. turn-on gate charge




Fig. 8 Typ. capacities, MOSFET only




Fig. 9 Typ. turn-on energy and switching times vs. collector current, inductive switching




Fig. 10 Typ. turn-off energy and switching times vs. collector-current, inductive switching




Fig. 11 Typ. turn-on energy and switching times vs. gate resistor, inductive switching




Fig. 12 Typ. turn-off energy and switching times vs. gate resistor, inductive switching




Fig. 13 Typ. forward characteristics of diode D




Fig. 14 Typ. reverse recovery characteristics of diode D




Fig. 15 Typ. reverse recovery characteristics of diode D



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.