




RESISTANCE @ +25°C = 100,000 Ω ± 2%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 MAXIMUM TEMPERATURE RATING = +300°C

LEAD WIRE: 26 AWG, STRANDED CONDUCTOR, TWO CONDUCTOR,  
 GLASS BRAID INSULATED, GLASS BRAID JACKETED CABLE,  
 0.060" X 0.052" NOMINAL O.D.

\*\*\* ROHS COMPLIANT \*\*\*

SEE MANUFACTURING SPECIFICATION (LAYER 1)

|      |                                                                                 |          |     |
|------|---------------------------------------------------------------------------------|----------|-----|
| "A"  | CABLE LENGTH WAS 120"±6",+ROHS NOTE,TERMINALS & CONN (WAS STRIPPED 0.3" ± 0.2") | 02/20/09 | DD  |
| NONE | RELEASE TO PRODUCTION                                                           | 02/19/09 | DD  |
| REV  | REVISION RECORD                                                                 | DATE     | APP |

|          |            |                                                                                                                                                  |
|----------|------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| SCALE    | NONE       | <b>U.S. SENSOR CORP.</b><br>1832 W. COLLINS AVE.<br>ORANGE, CA. 92867<br>714-639-1000 www.ussensor.com<br><b>THERMISTOR PROBE</b><br>P/N USP9728 |
| DRAWN BY | DAN DANKER |                                                                                                                                                  |
| DATE     | 02/19/09   |                                                                                                                                                  |
| REV.     | "A"        |                                                                                                                                                  |
| LAYER    | 0 OF 2     |                                                                                                                                                  |