




RESISTANCE @ +25°C = $5,000 \Omega \pm 10\%$
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = $-4.4\%/^{\circ}\text{C}$ NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 2 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = +150°C

---	ISO RELEASE	05/21/04	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP.	
DRAWN BY	T. WILFONG		
DATE	03/18/96	714-639-1000 www.ussensor.com	
REV.	NONE	NTC CHIP THERMISTOR	
LAYER	0 OF 1	P/N BC502J1K	

© COPYRIGHT