


0.020" $\pm$ 0.002" DIAMETER,
24 AWG, 1.0" LONG MINIMUM,
TIN PLATED CCS



RESISTANCE @ +25°C = 10,000 Ω $\pm$ 2%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA " β " (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED LIQUID)
 MAXIMUM OPERATING TEMPERATURE = +300°C

---	ISO RELEASE	10/24/03	DD
"A"	LEAD WIRE DIAMETER WAS 0.020" $\pm$ 0.001"	10/24/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com NTC THERMISTOR P/N 103JG1G	
DRAWN BY	T. SOMERVILLE		
DATE	10/26/90		
REV.	"A"		
LAYER	0 OF 1		