


- NOTES:
 1. MAX. RATING (SEE CHART), 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
 COVER MATERIAL: ALCRYN, BLACK
 3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
 4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC		FINISH
1	9	DRW	18	SCALE 1:1
2	10	PJM	19	DATE 9/4/01
3	12	CHK	20	DATE SUPER DRW
4	13	APPD	21	DATE RAW STK WT
5	14		23	LBS/M
6	15		33	TOLERANCE UNLESS OTHERWISE SPECIFIED
7	16		43	TWO PLACE DEC ±.01 FRACTION ±
8	17		53	THREE PLACE DEC ±.005 ANGULAR ±1°
TITLE				
MINIFUSE HOLDER, IN LINE				
LTR		REVISION		CHK APD
A		60655 - RELEASE 9/4/01 PJM		


 DES PLAINES, ILLINOIS 60016
 DRAWING NO. SERIES OUTLINE
 A 01530028Z

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT (STANDARD TEST METHOD AND TEST FUSE INSPECTION INSTRUCTIONS).
 DIMENSIONS OF DIMENSIONS--MINIMUM CP VALUE SHALL BE WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE DIMENSIONALLY LOCATED TO FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT