



- NOTES:
1. MAX. RATING, 20 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
 4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
MATL SPEC		FINISH		
COPIES TO	DRW	PJM	DATE	SCALE
1	9	18	10/15/01	1:1
2	10	19		SUPER DRW
3	12	20		
4	13	21		
5	14	23		RAW STK WT
6	15	33		LBS/M
7	16	43		TOLERANCE UNLESS OTHERWISE SPECIFIED
8	17	53		TWO PLACE DEC ±.01 FRACTION ±
				THREE PLACE DEC ±.005 ANGULAR ±1°
TITLE				
MINIFUSE HOLDER, IN LINE				
LTR		REVISION	CHK	APD
A	60683	RELEASE		
		10/15/01	PJM	

DES PLAINES, ILLINOIS 60016
 DRAWING NO. SERIES OUTLINE
 A 01530029Z

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT (STANDARD TEST METHOD). INSPECTOR MUST REFER TO INSTRUCTIONS.

DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS TO BE SHOWN ON THIS DRAWING APPLY TO THE DIMENSIONAL LOCATION TO BE SHOWN ON THIS DRAWING FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT