

# Axial Lead and Cartridge Fuses

## Ceramic Body

### 3.6 x 10 mm Fast-Acting Fuse 674 Series



- Designed to UL/CSA 248 Standard.
- Fast-Acting, ceramic body fuse in a compact package.
- This space saving fuse is ideally suited for lighting, power supply, and adapter applications.

#### ELECTRICAL CHARACTERISTICS:

% of Ampere Rating	Opening Time
100%	4 hours, Minimum
200%	5 seconds, Max.

**AGENCY APPROVALS:** Listed by Underwriters Laboratories and Certified by CSA from 0.100 through 8 Amps.

#### INTERRUPTING RATING:


50A@250V AC

#### PACKAGING OPTIONS:


Please refer to the following suffixes when ordering:  
 Bulk (1000 pieces): Add MXE suffix to the catalog part number.  
 Tape and Reel (1500 pieces): Add DRT4 suffix to the catalog part number.

#### TAPE AND REEL SPECIFICATIONS:

Per EIA-296 with 10mm pitch and 56.5mm inside tape spacing.



**674 000 Series**



Axial Lead Material: Solder coated copper.

#### ORDERING INFORMATION:

Catalog Number	Ampere Rating	Voltage Rating	Nominal Resistance Cold mOhms	Nominal Melting $i^2t$ A <sup>2</sup> Sec.
0674.100	.100	250	4.8150	0.00192
0674.125	.125	250	3.8540	0.00299
0674.200	.200	250	1.7300	0.0114
0674.250	.250	250	1.6100	0.0225
0674.300	.300	250	0.9395	0.0295
0674.400	.400	250	0.5860	0.0688
0674.500	.500	250	0.2325	0.128
0674.600	.600	250	0.1780	0.217
0674.750	.750	250	0.1320	0.250
0674.800	.800	250	0.1220	0.303
0674.001.	1.00	250	0.1050	0.506
0674.01.5	1.50	250	0.0592	0.881
0674.01.6	1.60	250	0.0560	0.951
0674.002.	2.00	250	0.0380	2.25
0674.02.5	2.50	250	0.0341	3.73
0674.3.15	3.15	250	0.0251	5.98
0674.004.	4.00	250	0.0175	8.96
0674.04.5	4.50	250	0.0171	9.58
0674.005.	5.00	250	0.0144	15.9
0674.006.	6.00	250	0.0131	18.0
0674.06.3	6.30	250	0.0120	19.2
0674.06.5	6.50	250	0.0119	21.6
0674.007.	7.00	250	0.0112	25.2
0674.008.	8.00	250	0.0088	35.4

#### Average Time Current Curves

