



- NOTES:
 1). RATING: NO: 14Vdc/35A
 NC: 14Vdc/20A
 2). TEMPERATURE RANGE: -40C TO 125C
 3). RELAY IS FLUX-TIGHT.
 4). ALL DIMENSIONS SHOWN FOR REFERENCE ONLY.

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

COPIES TO		MATL SPEC	
1	9	18	FINISH
2	10	19	DRW
3	12	20	CAD
4	13	21	CHK
5	14	23	APPD
6	15	33	SCALE
7	16	43	DATE
8	17	53	DATE
DIMENSION		TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)	
TOLERANCE		GRAMS/PIECE	
0.5 - 3	±0.05	3 - 6	±0.1
6 - 30	±0.05	6 - 30	±0.15
30 - 120	±0.1	120 - 400	±0.2
3RD ANGLE PROJECTION			
TITLE SINGLE POLE, DOUBLE THROW MICRO RELAY			
LTR		DATE	REVISION
A	06/24/09	000716ER	RELEASED
B	08/08/11	503010ERA-SEE	ERN GMB
C	04/18/12	504753ECA	ADD DIODE VERSION EJIN
CHK		APD	
CAD			
REVISION		DRWG. NO.	
C		02040090Z	

