


- NOTES:
1. THIS RETAINER IS SUPPLIED WITH THREE (3) SPRINGS, MAKING IT SUITABLE FOR 9, 14 + 20 AMP "SFE" FUSES BY SELECTING THE PROPER SPRING.
 2. FOR PANEL MOUNTING OF THIS RETAINER, ORDER SPRING CLIP -900-028.
 3. SPRINGS MAY BE SHIPPED ASSEMBLED EITHER INSIDE OR OUTSIDE OF FUSEHOLDER BODY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE 1.0
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. REFERENCE PROCEDURE FOR MEASUREMENT (S) IS TO BE FOUND IN THE DRAWING INSPECTION INSTRUCTIONS.
 DIMENSIONS CP DIMENSIONS.-MINIMUM CP VALUE SHALL BE WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE DRAWING UNLESS OTHERWISE SPECIFIED FOR MAXIMUM TOOL LIFE.

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
COPIES TO		MATL SPEC	FINISH	
1	9	DRW	JMB	DATE 1/12/98 SCALE 1=1
2	10	19	CHK	DATE SUPER DRW
3	12	20		DATE
4	13	21	APPD	DATE RAW STK WT
5	14	23		LBS/M
6	15	33		TOLERANCE UNLESS OTHERWISE SPECIFIED
7	16	43		TWO PLACE DEC ±
8	17	53		FRACTION ±
				THREE PLACE DEC ±.005
				ANGULAR ±1°
TITLE				
IN-LINE BAYONET KNOB FUSEHOLDER				
LTR		REVISION		CHK APD
C	38958C-	REVISED & REDRAWN ON NEW FORMAT	JMB	


 DES PLAINES, ILLINOIS 60016
 DRAWING NO. OUTFLINE OFHP0001Z
 C

UNCONTROLLED DOCUMENT