

Looking for a 2D Print?

Please visit the specific part number page to view the 2D print.

When viewing a series, please click on the specific part number you are looking for in the specifications table at the bottom of the page.

Specifications		Technical Resources			Related Products		Environmental Info		
Access specifications, certifications, check availability and order parts below									
Catalog #	Mounting Method	Fuse Type	Current Rating (Max)	Voltage Rating Max	Wire size	Ingress Protection	Temperature Maximum Celsius	Temperature Minimum Celsius	Compare
FHAS100	In-Line	ATO	20	32	12 AWG	IP67	85	-40	<input type="checkbox"/>
FHAS100-BP	In-Line	ATO	20	32	12 AWG	IP67	85	-40	<input type="checkbox"/>
FHAS101	In-Line	ATO	20	32	14 AWG	IP67	85	-40	<input type="checkbox"/>
FHMS200	In-Line	MINI	20	32	12 AWG	IP67	85	-40	<input type="checkbox"/>
FHMS200-BP				32	12 AWG	IP67	85	-40	<input type="checkbox"/>
FHMS201				32	14 AWG	IP67	85	-40	<input type="checkbox"/>

Once at the parts page, please scroll down to the bottom of the page and view the Technical Resources tab where you will find the part's 2D print and other part number related collateral.

Technical Resources		Environmental Info	
View All	Sealed In-Line ATO and MINI Fuse Holder FHAS100 2D Print Part Number: FHAS100 and FHAS100-BP,		
2D Prints			
Spotlights	Sealed In-Line ATO & MINI Fuse Holders Spotlight		
Datasheets	ATO-MINI-Sealed-Fuse-Holders Datasheet ATO-MINI-Sealed-Fuse-Holders Datasheet		
3D Model	3D Model - Sealed In-Line ATO & MINI Fuse Holders 3D Model 3D Model - Sealed In-Line ATO & MINI Fuse Holders 3D Model		
	Sealed In Line ATO MINI Fuse Holder Datasheet Sealed In Line ATO MINI Fuse Holder Datasheet		
	Sealed In-Line ATO and MINI Fuse Holder FHAS100 2D Print Part Number: FHAS100 and FHAS100-BP		