







SOCKETS

SOCKETS																										
Product	Features	Accessory For																								
<p>OT08PC Octal Socket 8-Pin</p> 	<p>8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 600VAC and has pressure clamp terminals.</p>	<p>AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes. Consult individual datasheet for compatibility</p>																								
<p>NDS-8 Octal Socket 8-Pin Screw terminals with captive wire clamps</p> 	<p>8-pin 35mm DIN rail or surface mount octal socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC8 hold-down clips.</p>	<p>Up to two #14 AWG (2.45 mm²) wire size Series: <table border="0"> <tr> <td>ARP</td> <td>FS500</td> <td>LLC4</td> <td>LLC5</td> </tr> <tr> <td>PRLM</td> <td>TDB</td> <td>TDBH</td> <td>TDBL</td> </tr> <tr> <td>TDI</td> <td>TDIH</td> <td>TDIL</td> <td>TDM</td> </tr> <tr> <td>TDMB</td> <td>TDMH</td> <td>TDML</td> <td>TDR</td> </tr> <tr> <td>TDS</td> <td>TDSH</td> <td>TDSL</td> <td>TRDU</td> </tr> <tr> <td>TRM</td> <td>TRS</td> <td>TRU</td> <td></td> </tr> </table> </p>	ARP	FS500	LLC4	LLC5	PRLM	TDB	TDBH	TDBL	TDI	TDIH	TDIL	TDM	TDMB	TDMH	TDML	TDR	TDS	TDSH	TDSL	TRDU	TRM	TRS	TRU	
ARP	FS500	LLC4	LLC5																							
PRLM	TDB	TDBH	TDBL																							
TDI	TDIH	TDIL	TDM																							
TDMB	TDMH	TDML	TDR																							
TDS	TDSH	TDSL	TRDU																							
TRM	TRS	TRU																								
<p>P1011-6 Octal Socket 8-Pin</p> 	<p>8-pin surface mount socket with binder head screw terminals. Rated at 10A @ 600VAC. UL Listed combination when used with TDM, TDB, TDS Series timers. Uses PSCRB8 hold-down brackets.</p>	<p>Series: <table border="0"> <tr> <td>ARP</td> <td>FS500</td> <td>LLC4</td> <td>LLC5</td> </tr> <tr> <td>PRLM</td> <td>TDB</td> <td>TDM</td> <td>TDMB</td> </tr> <tr> <td>TDR</td> <td>TDS</td> <td>TRB</td> <td>TRDU</td> </tr> <tr> <td>TRM</td> <td>TRS</td> <td>TRU</td> <td></td> </tr> </table> </p>	ARP	FS500	LLC4	LLC5	PRLM	TDB	TDM	TDMB	TDR	TDS	TRB	TRDU	TRM	TRS	TRU									
ARP	FS500	LLC4	LLC5																							
PRLM	TDB	TDM	TDMB																							
TDR	TDS	TRB	TRDU																							
TRM	TRS	TRU																								
<p>OT11PC Magnal Socket 11-Pin</p> 	<p>Magnal Sockets are for plug-in units</p>	<p>11-pin Plug-in units Series: <table border="0"> <tr> <td>ARP</td> <td>LLC6</td> <td>TDB</td> <td>TDBH</td> </tr> <tr> <td>TDBL</td> <td>TDMB</td> <td>TDS</td> <td>TDSH</td> </tr> <tr> <td>TDSL</td> <td>TRB</td> <td>TRDU</td> <td>TRM</td> </tr> <tr> <td>TRS</td> <td>TRU</td> <td></td> <td></td> </tr> </table> </p>	ARP	LLC6	TDB	TDBH	TDBL	TDMB	TDS	TDSH	TDSL	TRB	TRDU	TRM	TRS	TRU										
ARP	LLC6	TDB	TDBH																							
TDBL	TDMB	TDS	TDSH																							
TDSL	TRB	TRDU	TRM																							
TRS	TRU																									
<p>SD12-PC Rectangle Socket 12-pin</p> 	<p>12-pin surface Rectangle Socket.</p>	<p>ACBC-120</p>																								
<p>NDS-11 11-pin Magnal Socket Screw terminals with captive wire clamps</p> 	<p>11 pin 35 mm DIN rail or surface mount socket. Rated at 10A @ 300VAC. Surface mounted with two #6 (M 3.5 x 0.6) screws or snaps onto a 35 mm DIN rail. A spring mechanism allows easy removal. Uses PSC11 hold-down clips.</p>	<p>AWG 12 to 22 (3.2 to 0.33 mm²) wire sizes Series: <table border="0"> <tr> <td>ARP</td> <td>LLC6</td> <td>TDB</td> <td>TDBH</td> </tr> <tr> <td>TDBL</td> <td>TDMB</td> <td>TDS</td> <td>TDSH</td> </tr> <tr> <td>TDSL</td> <td>TRB</td> <td>TRDU</td> <td>TRM</td> </tr> <tr> <td>TRS</td> <td>TRU</td> <td></td> <td></td> </tr> </table> </p>	ARP	LLC6	TDB	TDBH	TDBL	TDMB	TDS	TDSH	TDSL	TRB	TRDU	TRM	TRS	TRU										
ARP	LLC6	TDB	TDBH																							
TDBL	TDMB	TDS	TDSH																							
TDSL	TRB	TRDU	TRM																							
TRS	TRU																									