

$\varnothing 33.2 \pm 0.18$
 $[\varnothing 1.306 \pm 0.007]$

4.8 ± 0.08
 $[0.188 \pm 0.003]$

7.9 ± 0.13
 $[0.312 \pm 0.005]$

95.50 ± 1.59
 $[3.760 \pm 0.063]$

90.73 ± 1.59
 $[3.572 \pm 0.063]$

112.2 ± 1.59
 $[4.416 \pm 0.063]$

74.1 ± 1.59
 $[2.916 \pm 0.063]$

25.4 ± 0.20
 $[1.000 \pm 0.008]$

REVISION

REV	DATE	DESCRIPTION
A	7/19/23	526717GCP - RELEASE MRY

1	COMPONENT NO	DESCRIPTION	QTY/M	U/M
---	--------------	-------------	-------	-----

BILL OF MATERIAL

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE			
●	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.			A

MATL SPEC		FINISH		
DRW JMoler	DATE 6/23/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION



TITLE L60S 125-200A OUTLINE



REVISION A	DRWG NO. OL-L60S200	SHEET 1 OF 1
----------------------	-------------------------------	--------------