

# Installation Instructions for ISS-102ACI-MC Intrinsically-Safe Switch

**WARNING:** TO PREVENT IGNITION OF FLAMMABLE OR COMBUSTABLE ATMOSPHERES, DISCONNECT POWER FROM THE SYSTEM PRIOR TO INSTALLATION OR SERVICE.

**CAUTION:** Installation must comply with all national, state, and local codes. Installation of this equipment should only be performed by personnel trained in intrinsically-safe systems. Improper installation may result in serious injury or damage. Before proceeding with installation, read and understand these instructions completely.


The ISS-102 Isolated Switch is UL913 listed (E233355) as an associated apparatus for interfacing between hazardous and non-hazardous areas. The ISS-102 must be installed in a non-hazardous area. Follow SymCom's Control Drawing ISS-102ACI on page 4 for proper installation.

All wiring connected to a hazardous location must be separated from all non-intrinsically-safe wiring. Description of special wiring methods can be found in the National Electrical Code ANSI/NFPA 70, Article 504 Intrinsically-Safe Systems. Check your state and local codes for additional requirements.

**WARNING: REMOVE POWER FROM THE SYSTEM PRIOR TO INSTALLING OR SERVICING THE ISS-102.**

## INSTALLATION

1. Mount the ISS-102 in a non-hazardous location on 35mm DIN rail, or by installing two #6 or #8 screws into the surface mounting holes provided.
2. Connect wiring per SymCom's Control Drawing ISS-102ACI on page 4. Follow all hazardous code requirements while installing wiring to switch input terminals.



## OPERATION

The ISS-102ACI-MC (Multi-function Controller) is user-configurable as a single or dual-channel switch, or pump-up/pump-down controller. The intrinsically-safe inputs are compatible with normally open (N.O.) or normally closed (N.C.) switches, as well as resistive probes. **NOTE: Prior to installation, set the DIP switches according to your specific system configuration (refer to Table 1).**

DIP SWITCH*	DESCRIPTION	SWITCH POSITION (ON = ↑, OFF = ↓)
S1, S2	MODE SELECT	OFF, OFF = Differential/Latching Logic
		ON, OFF = 1-Channel Switch
		OFF, ON = 2-Channel Switch
S3	LOGIC	OFF = Direct Logic
		ON = Inverted Logic
S4	DEBOUNCE	OFF = .5 second
		ON = 2 seconds

\*S1, S2, S3, and S4 refer to the DIP switches on the side of the ISS-102.

**TABLE 1: Setting the DIP Switches**

## Definitions

**Normally Open (N.O.)** – switch is “open” when water is **not** present

**Normally Closed (N.C.)** – switch is “closed” when water is **not** present

**Direct Logic** – input channels are active when “low” resistance (or closed switch) is detected

**Inverted Logic** – input channels are active when “high” resistance (or open switch) is detected

**Debounce** – the time delay required between changes of state (prevents nuisance tripping)

**Sensitivity** – resistance level required to change the state of the input channels

**NOTE: if using resistive probes, set the sensitivity to the desired resistance limit, 4.7–100kΩ. If using switches, set the sensitivity to 100kΩ.**

**LED1 and LED2** – Each LED illuminates when its corresponding output relay is energized

## Single-Channel Switch Mode

In single-channel switch mode, RELAY 1 (form A) and RELAY 2 (form C) will energize when **CH1** is activated (CH2 is disabled in this mode). Refer to Table 2 for proper DIP switch configuration.

FUNCTION	S1	S2	S3
1-Channel Switch with Direct Logic	ON	OFF	OFF
1-Channel Switch with Inverted Logic	ON	OFF	ON

**TABLE 2: Single-Channel Mode**

## Dual-Channel Switch (non-latching)

In dual-channel mode, RELAY 1 (form A) will energize when **CH1** is activated, and RELAY 2 (form C) will energize when **CH2** is activated. Refer to Table 3 for proper DIP switch configuration.

FUNCTION	S1	S2	S3
2-Channel Switch with Direct Logic	OFF	ON	OFF
2-Channel Switch with Inverted Logic	OFF	ON	ON

**TABLE 3: Dual-Channel Non-Latching Mode**

## Dual-Channel Differential / Latching Mode

### Normally-Open (N.O.) Switches or Resistive Probes:

**Pump-Down:** Connect the **lower** float/probe to **CH1** (lead) and the **upper** float/probe to **CH2** (lag). Once the water level in the tank rises enough to activate the lag input, both output relays will energize and turn on the pump. After enough water is pumped from the tank to deactivate the lead input, the relays will de-energize and turn off the pump. Refer to Table 4 for proper DIP switch configuration.

FUNCTION	S1	S2	S3
Pump-Down with N.O. Switches or Resistive Probes (see Examples 1 & 2)	OFF	OFF	OFF

**TABLE 4: Dual-Channel Latching Mode**

**Pump-Up:** Connect the **upper** float/probe to **CH1** (lead) and the **lower** float/probe to **CH2** (lag). Once the water level in the tank drops enough to activate the lag input, both output relays will energize and turn on the pump. After enough water is pumped into the tank to deactivate the lead input, the relays will de-energize and turn off the pump. Refer to Table 5 for proper switch configuration.

FUNCTION	S1	S2	S3
Pump-Up with N.O. Switches or Resistive Probes (see Examples 3 & 4)	OFF	OFF	ON

**2 TABLE 5: Dual-Channel Latching Mode**

## Dual-Channel Differential / Latching Mode (cont.)

### Normally-Closed (N.C.) Switches:

**Pump-Down:** Connect the **lower** float to **CH1** (lead) and the **upper** float/probe to **CH2** (lag). Once the water level in the tank rises enough to activate the lag input, both output relays will energize and turn on the pump. After enough water is pumped from the tank to deactivate the lead input, the relays will de-energize and turn off the pump. Refer to Table 6 for proper DIP switch configuration.

FUNCTION	S1	S2	S3
Pump-Down with N.C. Switches (see Example 5)	OFF	OFF	ON

TABLE 6: Dual-Channel Latching Mode


**Pump-Up:** Connect the **upper** float to **CH1** (lead) and the **lower** float/probe to **CH2** (lag). Once the water level in the tank drops enough to activate the lag input, both output relays will energize and turn on the pump. After deactivate the lead input, the relays will de-energize and turn off the pump. Refer to Table 7 for proper DIP switch configuration.

FUNCTION	S1	S2	S3
Pump-Up with N.C. Switches (see Example 6)	OFF	OFF	OFF


TABLE 7: Dual-Channel Latching Mode

## EXAMPLE WIRING DIAGRAMS (examples apply to Differential / Latching Mode only)


EXAMPLE 1:  
Pump-Down with  
N.O. Switches




EXAMPLE 2:  
Pump-Down with  
Probes




EXAMPLE 3:  
Pump-Up with  
N.O. Switches




EXAMPLE 4:  
Pump-Up  
with Probes



EXAMPLE 5:  
Pump-Down with  
N.C. Switches



EXAMPLE 6:  
Pump-Up with  
N.C. Switches



# CONTROL DRAWING ISS-102ACI

## ASSOCIATED APPARATUS / APPAREILLAGE CONNEXE

### Non-Hazardous Location

**Supply Voltage**  
120VAC

**Relay Output Rating**  
5 Amps @ 120VAC General Purpose  
Pilot Duty 180VA @ 120VAC, C150

**Maximum Ambient Temperature Rating**  
55°C


**DEVICE MUST BE INSTALLED IN A SUITABLE ENCLOSURE**

**WARNING!**  
**TO PREVENT IGNITION OF FLAMMABLE OR COMBUSTABLE**  
**ATMOSPHERES, DISCONNECT POWER BEFORE SERVICING.**

**DEVICE MAY ONLY BE REPAIRED BY THE MANUFACTURER**

**WARNING!**  
**SUBSTITUTION OF COMPONENTS MAY IMPAIR INTRINSIC SAFETY.**

**AVERTISSEMENT!**  
**LA SUBSTITUTION DE COMPOSANTS PEUT COMPROMETTRE LA**  
**SÉCURITÉ INTRINSÈQUE.**



### Hazardous Location

Class I, Divisions I & II, Groups A, B, C & D;  
Class II, Divisions I & II, Groups E, F & G; and  
Class III locations

**NOTES:**

1. Maximum distance between unit and switch contact is 10,000 feet.
2. All non-intrinsically safe wiring shall be separated from intrinsically safe wiring. Description of special wiring methods can be found in the National Electrical Code ANSI/NFPA 70, Article 504 Intrinsically Safe Systems. Check your state and local codes for additional requirements.
3. All switch contacts shall be non-energy storing, containing no inductance or capacitance.
4. Entity Parameters:  

$V_{oc} = 16.8V$	$C_a = 0.39\mu F$
$I_{sc} = 1.2mA$	$P_o = \frac{V_{oc} \cdot I_{sc}}{4}$
$L_a = 100mH$	

5. Entity Parameter Relationships:

<u>IS Equipment</u>	≥	<u>Associated Apparatus</u>
$V_{max}$ (or $U_i$ )	≥	$V_{oc}$ or $V_t$ (or $U_o$ )
$I_{max}$ (or $I_i$ )	≥	$I_{sc}$ or $I_t$ (or $I_o$ )
$P_{max}$ , $P_i$	≥	$P_o$
$C_i + C_{cable}$	≤	$C_a$ (or $C_o$ )
$L_i + L_{cable}$	≤	$L_a$ (or $L_o$ )

Capacitance and inductance of the field wiring from the intrinsically-safe equipment to the associated apparatus shall be calculated and must be included in the system calculations as shown in the table above. Cable capacitance,  $C_{cable}$ , plus intrinsically-safe equipment capacitance,  $C_i$ , must be less than the marked capacitance,  $C_a$  (or  $C_o$ ), shown on any associated apparatus used. The same applies for inductance ( $L_{cable}$ ,  $L_i$  and  $L_a$  or  $L_o$ , respectively). Where the cable capacitance and inductance per foot are not known, the following values shall be used:  $C_{cable} = 60pF/ft.$ ,  $L_{cable} = 0.2\mu H/ft.$