

Ø63.5 ± 0.38
[Ø2.500 ± 0.015]

9.5 ± 0.15
[0.375 ± 0.006]

13.5 ± 0.25
[0.531 ± 0.010]

108.73 ± 1.60
[4.281 ± 0.063]

117.47 ± 1.60
[4.625 ± 0.063]

56.4
[2.219]

164.3 ± 1.60
[6.469 ± 0.063]

50.8 ± 0.89
[2.000 ± 0.035]

REVISION

REV	DATE	DESCRIPTION
A	7/6/23	526696GCP - RELEASE MRY

1	NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
---	----	--------------	-------------	-------	-----

BILL OF MATERIAL

<S>	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE				
●	DENOTES CRITICAL CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
⊠	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.				A

MATL SPEC	FINISH			
-----------	--------	--	--	--

DRW JMoler	DATE 6/22/2023	SCALE NTS	FINISH GOOD WT GRAMS/PIECE	
---------------	-------------------	--------------	-------------------------------	--

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE PROJECTION	
-------------------------	--

TITLE L50S 700-800A OUTLINE



REVISION A	DRWG NO. OL-L50S800	SHEET 1 OF 1
----------------------	-------------------------------	--------------