


**GenX3™ 600V IGBT**
**IXGN72N60A3**

 Ultra Low V<sub>sat</sub> PT IGBT for  
up to 5kHz switching


$$V_{CES} = 600V$$


$$I_{C110} = 68A$$

$$V_{CE(sat)} \leq 1.35V$$

| Symbol                        | Test Conditions   | Maximum Ratings                         |                          |
|-------------------------------|---|---|--------------------------|
| $V_{CES}$                     | $T_J = 25^\circ C$ to $150^\circ C$   | 600                                     | V                        |
| $V_{CGR}$                     | $T_J = 25^\circ C$ to $150^\circ C$ , $R_{GE} = 1M\Omega$                           | 600                                     | V                        |
| $V_{GES}$                     | Continuous  | $\pm 20$                                | V                        |
| $V_{GEM}$                     | Transient   | $\pm 30$                                | V                        |
| $I_{C25}$                     | $T_C = 25^\circ C$ (Chip capability)  | 160                                     | A                        |
| $I_{C110}$                    | $T_C = 110^\circ C$   | 68                                      | A                        |
| $I_{LRMS}$                    | Terminal Current Limit  | 100                                     | A                        |
| $I_{CM}$                      | $T_C = 25^\circ C$ , 1ms  | 400                                     | A                        |
| <b>SSOA</b><br><b>(RBSOA)</b> | $V_{GE} = 15V$ , $T_{VJ} = 125^\circ C$ , $R_G = 3\Omega$<br>Clamped inductive load | $I_{CM} = 150$<br>@ $0.8 \cdot V_{CES}$ | A                        |
| $P_C$                         | $T_C = 25^\circ C$  | 360                                     | W                        |
| $T_J$                         |   | -55 ... +150                            | $^\circ C$               |
| $T_{JM}$                      |   | 150                                     | $^\circ C$               |
| $T_{stg}$                     |   | -55 ... +150                            | $^\circ C$               |
| $V_{ISOL}$                    | 50/60Hz<br>$I_{ISOL} \leq 1mA$  | $t = 1min$<br>$t = 1s$                  | 2500<br>3000<br>V~<br>V~ |
| $M_d$                         | Mounting torque<br>Terminal connection torque (M4)                                  | 1.5/13<br>1.3/11.5                      | Nm/lb.in.<br>Nm/lb.in.   |
| <b>Weight</b>                 |   | 30                                      | g                        |

**SOT-227B, miniBLOC**

E153432



G = Gate, C = Collector, E = Emitter

 ① Either emitter terminal can be used as  
Main or Kelvin Emitter

**Features**

- Optimized for low conduction losses
- Isolation voltage 3000 V~
- Square RBSOA
- International standard package

**Advantages**

- High power density
- Low gate drive requirement

**Applications**

- Power Inverters
- UPS
- Motor Drives
- SMPS
- PFC Circuits
- Battery Chargers
- Welding Machines
- Lamp Ballasts
- Inrush Current Protection Circuits

| Symbol        | Test Conditions<br>( $T_J = 25^\circ C$ , unless otherwise specified) | Characteristic Values |      |                           |
|---------------|---|-----------------------|------|---------------------------|
|               |   | Min.                  | Typ. | Max.                      |
| $BV_{CES}$    | $I_C = 250\mu A$ , $V_{GE} = 0V$                                      | 600                   |      | V                         |
| $V_{GE(th)}$  | $I_C = 250\mu A$ , $V_{CE} = V_{GE}$                                  | 3.0                   |      | 5.0 V                     |
| $I_{CES}$     | $V_{CE} = V_{CES}$<br>$V_{GE} = 0V$<br>$T_J = 125^\circ C$            |                       |      | 75 $\mu A$<br>750 $\mu A$ |
| $I_{GES}$     | $V_{CE} = 0V$ , $V_{GE} = \pm 20V$                                    |                       |      | $\pm 100$ nA              |
| $V_{CE(sat)}$ | $I_C = 60A$ , $V_{GE} = 15V$ , Note 1                                 |                       |      | 1.35 V                    |

| Symbol       | Test Conditions<br>( $T_J = 25^\circ\text{C}$ , unless otherwise specified)   | Characteristic Values |      |                    |
|--------------|---|-----------------------|------|--------------------|
|              |   | Min.                  | Typ. | Max.               |
| $g_{fs}$     | $I_C = 60\text{A}$ , $V_{CE} = 10\text{V}$ , Note 1   | 48                    | 76   | S                  |
| $C_{ies}$    | $V_{CE} = 25\text{V}$ , $V_{GE} = 0\text{V}$ , $f = 1\text{MHz}$  |                       | 6600 | pF                 |
| $C_{oes}$    |   |                       | 360  | pF                 |
| $C_{res}$    |   |                       | 80   | pF                 |
| $Q_{g(on)}$  | $I_C = 60\text{A}$ , $V_{GE} = 15\text{V}$ , $V_{CE} = 0.5 \cdot V_{CES}$   |                       | 230  | nC                 |
| $Q_{ge}$     |   |                       | 40   | nC                 |
| $Q_{gc}$     |   |                       | 78   | nC                 |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 25^\circ\text{C}</math></b><br>$I_C = 50\text{A}$ , $V_{GE} = 15\text{V}$<br>$V_{CE} = 480\text{V}$ , $R_G = 3\Omega$  |                       | 31   | ns                 |
| $t_{ri}$     |   |                       | 34   | ns                 |
| $E_{on}$     |   |                       | 1.38 | mJ                 |
| $t_{d(off)}$ |   |                       | 320  | ns                 |
| $t_{fi}$     |   |                       | 250  | ns                 |
| $E_{off}$    |   |                       | 3.5  | mJ                 |
| $t_{d(on)}$  | <b>Inductive load, <math>T_J = 125^\circ\text{C}</math></b><br>$I_C = 50\text{A}$ , $V_{GE} = 15\text{V}$<br>$V_{CE} = 480\text{V}$ , $R_G = 3\Omega$ |                       | 29   | ns                 |
| $t_{ri}$     |   |                       | 32   | ns                 |
| $E_{on}$     |   |                       | 2.6  | mJ                 |
| $t_{d(off)}$ |   |                       | 510  | ns                 |
| $t_{fi}$     |   |                       | 375  | ns                 |
| $E_{off}$    |   |                       | 6.5  | mJ                 |
| $R_{thJC}$   |   |                       | 0.35 | $^\circ\text{C/W}$ |
| $R_{thCK}$   |   | 0.05                  |      | $^\circ\text{C/W}$ |

## SOT-227B miniBLOC (IXGN)



| SYM | INCHES |       | MILLIMETERS |       |
|-----|--------|-------|-------------|-------|
|     | MIN    | MAX   | MIN         | MAX   |
| A   | 1.240  | 1.255 | 31.50       | 31.88 |
| B   | .307   | .323  | 7.80        | 8.20  |
| C   | .161   | .169  | 4.09        | 4.29  |
| D   | .161   | .169  | 4.09        | 4.29  |
| E   | .161   | .169  | 4.09        | 4.29  |
| F   | .587   | .595  | 14.91       | 15.11 |
| G   | 1.186  | 1.193 | 30.12       | 30.30 |
| H   | 1.496  | 1.505 | 38.00       | 38.23 |
| J   | .460   | .481  | 11.68       | 12.22 |
| K   | .351   | .378  | 8.92        | 9.60  |
| L   | .030   | .033  | 0.76        | 0.84  |
| M   | .496   | .506  | 12.60       | 12.85 |
| N   | .990   | 1.001 | 25.15       | 25.42 |
| O   | .078   | .084  | 1.98        | 2.13  |
| P   | .195   | .235  | 4.95        | 5.97  |
| Q   | 1.045  | 1.059 | 26.54       | 26.90 |
| R   | .155   | .174  | 3.94        | 4.42  |
| S   | .186   | .191  | 4.72        | 4.85  |
| T   | .968   | .987  | 24.59       | 25.07 |
| U   | -.002  | .004  | -0.05       | 0.1   |

Note: 1. Pulse test,  $t \leq 300\mu\text{s}$ ; duty cycle,  $d \leq 2\%$ .

### PRELIMINARY TECHNICAL INFORMATION


The product presented herein is under development. The Technical Specifications offered are derived from data gathered during objective characterizations of preliminary engineering lots; but also may yet contain some information supplied during a pre-production design evaluation. IXYS reserves the right to change limits, test conditions, and dimensions without notice.

IXYS reserves the right to change limits, test conditions, and dimensions.


IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents:

|           |           |           |           |              |              |              |              |              |             |
|-----------|-----------|-----------|-----------|--------------|--------------|--------------|--------------|--------------|-------------|
| 4,835,592 | 4,931,844 | 5,049,961 | 5,237,481 | 6,162,665    | 6,404,065 B1 | 6,683,344    | 6,727,585    | 7,005,734 B2 | 7,157,338B2 |
| 4,850,072 | 5,017,508 | 5,063,307 | 5,381,025 | 6,259,123 B1 | 6,534,343    | 6,710,405 B2 | 6,759,692    | 7,063,975 B2 |             |
| 4,881,106 | 5,034,796 | 5,187,117 | 5,486,715 | 6,306,728 B1 | 6,583,505    | 6,710,463    | 6,771,478 B2 | 7,071,537    |             |


**Fig. 1. Output Characteristics @ 25°C**




**Fig. 2. Extended Output Characteristics @ 25°C**




**Fig. 3. Output Characteristics @ 125°C**




**Fig. 4. Dependence of VCE(sat) on Junction Temperature**




**Fig. 5. Collector-to-Emitter Voltage vs. Gate-to-Emitter Voltage**




**Fig. 6. Input Admittance**




**Fig. 7. Transconductance**




**Fig. 8. Gate Charge**




**Fig. 9. Capacitance**









**Fig. 10. Reverse-Bias Safe Operating Area**




**Fig. 11. Maximum Transient Thermal Impedance**




**Fig. 12. Inductive Switching Energy Loss vs. Gate Resistance**

**Fig. 13. Inductive Switching Energy Loss vs. Collector Current**

**Fig. 14. Inductive Switching Energy Loss vs. Junction Temperature**

**Fig. 15. Inductive Turn-off Switching Times vs. Gate Resistance**

**Fig. 16. Inductive Turn-off Switching Times vs. Collector Current**

**Fig. 17. Inductive Turn-off Switching Times vs. Junction Temperature**



**Fig. 18. Inductive Turn-on  
Switching Times vs. Gate Resistance**



**Fig. 19. Inductive Turn-on  
Switching Times vs. Collector Current**



**Fig. 20. Inductive Turn-on  
Switching Times vs. Junction Temperature**





---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).