


# CoolMOS™ 1) Power MOSFET

with Series Schottky Diode and  
Ultra Fast Antiparallel Diode


in High Voltage ISOPLUS i4-PAC™

Preliminary data



$V_{DSS} = 600\text{ V}$   
 $I_{D25} = 41\text{ A}$   
 $R_{DS(on) \text{ typ.}} = 60\text{ m}\Omega$   
 $t_{rr} = 70\text{ ns}$

ISOPLUS i4-PAC™



MOSFET T					
Symbol	Conditions	Maximum Ratings			
$V_{DSS}$	$T_{VJ} = 25^\circ\text{C to } 150^\circ\text{C}$	600	V		
$V_{GS}$		$\pm 20$	V		
$I_{D25}$	$T_C = 25^\circ\text{C}$	41	A		
$I_{D90}$	$T_C = 90^\circ\text{C}$	29	A		
Symbol	Conditions	Characteristic Values			
( $T_{VJ} = 25^\circ\text{C}$ , unless otherwise specified)					
		min.	typ.	max.	
$R_{DSon}$	MOSFET 'T' only:				
	$V_{GS} = 10\text{ V}; I_D = 25\text{ A}$		60	70	$\text{m}\Omega$
		$T_{VJ} = 25^\circ\text{C}$			
		$T_{VJ} = 125^\circ\text{C}$		135	$\text{m}\Omega$
	MOSFET 'T & $D_S$ ' in series (pin 5, pin 2):				
	$V_{GS} = 10\text{ V}; I_D = 10\text{ A}$	$T_{VJ} = 25^\circ\text{C}$	120		$\text{m}\Omega$
	$T_{VJ} = 125^\circ\text{C}$	170		$\text{m}\Omega$	
	$V_{GS} = 10\text{ V}; I_D = 25\text{ A}$	$T_{VJ} = 25^\circ\text{C}$	85		$\text{m}\Omega$
	$T_{VJ} = 125^\circ\text{C}$	145		$\text{m}\Omega$	
$V_{GS(th)}$	$V_{DS} = 20\text{ V}; I_D = 3\text{ mA}$	2.1		3.9	V
$I_{DSS}$	$V_{DS} = V_{DSS}; V_{GS} = 0\text{ V}$			0.3	$\text{mA}$
			1		$\text{mA}$
$I_{GSS}$	$V_{GS} = \pm 20\text{ V}; V_{DS} = 0\text{ V}$			100	nA
$Q_g$	$V_{GS} = 10\text{ V}; V_{DS} = 350\text{ V}; I_D = 50\text{ A}$		250		nC
$Q_{gs}$			25		nC
$Q_{gd}$			120		nC
$t_{d(on)}$	Inductive load $V_{GS} = 10\text{ V}; V_{DS} = 380\text{ V}$ $I_D = 25\text{ A}; R_G = 10\ \Omega$	$T_{VJ} = 125^\circ\text{C}$		30	ns
$t_r$				18	ns
$t_{d(off)}$				500	ns
$t_f$				50	ns
$E_{on}$				0.7	mJ
$E_{off}$				0.3	mJ
$E_{rec(off)}$				0.22	mJ
$R_{thJC}$			with heatsink compound (IXYS test setup)		0.45
$R_{thJH}$	0.5	0.7		K/W	

## Features

- fast CoolMOS™ 1) power MOSFET 3<sup>rd</sup> generation
  - high blocking voltage
  - low on resistance
  - low thermal resistance due to reduced chip thickness
- Series Schottky diode prevents current flow through MOSFET's body diode
  - very low forward voltage
  - fast switching
- Ultra fast HiPerFRED™ anti parallel diode
  - low operating forward voltage
  - fast and soft reverse recovery
  - low switching losses
- ISOPLUS i4-PAC™ high voltage package
  - isolated back surface
  - low coupling capacity between pins and heatsink
  - enlarged creepage towards heatsink
  - enlarged creepage betw. high voltage pins
  - application friendly pinout
  - high reliability
  - industry standard outline
  - UL registered E 72873

## Applications

- Converters with
- circuit operation leading to current flow through switches in reverse direction - e. g.
    - phaseleg with inductive load
    - resonant circuits
  - high switching frequency

## Examples

- switched mode power supplies (SMPS)
- uninterruptable power supplies (UPS)
- DC-DC converters
- welding converters
- converters for inductive heating
- drive converters

1) CoolMOS™ is a trademark of Infineon Technologies AG.

**Series Schottky Diode D<sub>s</sub>**

Symbol	Conditions	Maximum Ratings		
I <sub>F25</sub>	T <sub>C</sub> = 25°C		77	A
I <sub>F90</sub>	T <sub>C</sub> = 90°C		45	A

Symbol	Conditions	Characteristic Values		
(T <sub>VJ</sub> = 25°C, unless otherwise specified)				
		min.	typ.	max.
V <sub>F</sub>	I <sub>F</sub> = 20 A; T <sub>C</sub> = 25°C		0.71	V
	T <sub>C</sub> = 125°C	0.5		V
V <sub>T0</sub>	} T <sub>VJ</sub> = 150°C for power loss calculation only		0.42	V
r <sub>T</sub>			4.1	mΩ
R <sub>thJC</sub>	with heatsink compound (IXYS test setup)		2.2	K/W
R <sub>thJH</sub>		2.8	3.5	K/W

**Free Wheeling Diode D<sub>F</sub>**

Symbol	Conditions	Maximum Ratings		
I <sub>F25</sub>	T <sub>C</sub> = 25°C		40	A
I <sub>F90</sub>	T <sub>C</sub> = 90°C		23	A


Symbol	Conditions	Characteristic Values		
(T <sub>VJ</sub> = 25°C, unless otherwise specified)				
		typ.	max.	
V <sub>F</sub>	I <sub>F</sub> = 30 A; T <sub>C</sub> = 25°C	2.1	2.5	V
	T <sub>C</sub> = 125°C	1.4		V
V <sub>T0</sub>	} T <sub>VJ</sub> = 150°C for power loss calculation only		1.0	V
r <sub>T</sub>			17.3	mΩ
I <sub>RM</sub>	} I <sub>F</sub> = 25 A; di <sub>F</sub> /dt = -400 A/μs; T <sub>VJ</sub> = 125°C	15		A
t <sub>rr</sub>		V <sub>R</sub> = 380 V; V <sub>GE</sub> = 0 V	110	
R <sub>thJC</sub>	with heatsink compound (IXYS test setup)		1.8	K/W
R <sub>thJH</sub>		2.3	2.5	K/W

**Component**

Symbol	Conditions	Maximum Ratings		
T <sub>VJ</sub>	operating	-40...+150		°C
T <sub>stg</sub>	storage	-40...+125		°C
V <sub>ISOL</sub>	I <sub>ISOL</sub> = 1 mA, 50/60 Hz, t = 1 min	3000		V~
F <sub>C</sub>	mounting force with clip	20-120		N

Symbol	Conditions	Characteristic Values		
		min.	typ.	max.
C <sub>p</sub>	coupling capacity between shorted pins and mounting tab in the case		40	pF
d <sub>s</sub> , d <sub>A</sub>	D pin - S pin	7		mm
d <sub>s</sub> , d <sub>A</sub>	pin - backside metal	5.5		mm
Weight			6	g

**ISOPLUS i4-PAC™ Outline**


Dim.	Millimeter		Inches	
	min	max	min	max
A	4.83	5.21	0.190	0.205
A1	2.59	3.00	0.102	0.118
A2	1.17	2.16	0.046	0.085
b	1.14	1.40	0.045	0.055
b2	1.47	1.73	0.058	0.068
b4	2.54	2.79	0.100	0.110
c	0.51	0.74	0.020	0.029
D	20.80	21.34	0.819	0.840
D1	14.99	15.75	0.590	0.620
D2	1.65	2.03	0.065	0.080
D3	20.30	20.70	0.799	0.815
E	19.56	20.29	0.770	0.799
E1	16.76	17.53	0.660	0.690
e	3.81 BSC		0.150 BSC	
e1	11.43 BSC		0.450 BSC	
L	19.81	21.34	0.780	0.840
L1	2.11	2.59	0.083	0.102
Q	5.33	6.20	0.210	0.244
R	2.54	4.57	0.100	0.180
W	-	0.10	-	0.004

Die konvexe Form des Substrates ist typ. < 0.05 mm über der Kunststoffoberfläche der Bauteilunterseite  
 The convex bow of substrate is typ. < 0.05 mm over plastic surface level of device bottom side




Fig. 1 Drain source breakdown voltage  $V_{DSS}$  vs. junction temperature  $T_J$




Fig. 2 Typical transfer characteristic




Fig. 3 Typical output characteristic (between pin 5 and pin 2)




Fig. 4 Typical output characteristic (between pin 5 and pin 2)




Fig. 5 Drain source on-state resistance  $R_{DS(on)}$  versus junction temperature  $T_J$  (between pin 5 and pin 2)




Fig. 6 Drain source on-state resistance  $R_{DS(on)}$  versus  $I_D$  (between pin 5 and pin 2)




Fig. 7 Typical output characteristic (MOSFET only)




Fig. 8 Typical output characteristic (MOSFET only)




Fig. 9 Drain source on-state resistance  $R_{DS(on)}$  versus junction temperature  $T_J$  (MOSFET only)




Fig. 10 Drain source on-state resistance  $R_{DS(on)}$  versus  $I_D$  (MOSFET only)




Fig. 11 Gate charge characteristic




Fig. 12 Drain current  $I_D$  vs. case temperature  $T_C$




Fig. 13 Typ. turn-on energy & switching times vs. collector current, inductive switching




Fig. 14 Typ. turn-off energy & switching times vs. collector current, inductive switching




Fig. 15 Typ. turn-on energy & switching times vs. gate resistor, inductive switching




Fig. 16 Typ. turn-off energy & switching times vs. gate resistor, inductive switching




Fig. 17 Typ. forward characteristics of reverse diode




Fig. 18 Typ. reverse recovery characteristics of antiparallel diode




Fig. 19 Typ. reverse recovery characteristics




Fig. 20 Typ. forward characteristics of diode D<sub>S</sub>




Fig. 21 Typ. thermal impedance junction to heatsink  $Z_{thJH}$  of the MOSFET with heat transfer paste




Fig. 22 Typ. thermal impedance junction to heatsink  $Z_{thJH}$  of the Diodes with heat transfer paste



---

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).